



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	6	RELEASED AS PER ECO-17-009529	03JUL2017	PV	MP

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:

Raychem Connector Code: 41
 Connector Series: MIL-C-38999 SERIES 1 & 2
 Adaptor Series: 204M0**-19-B**-K-NS (Olive Drab);
 Aluminium Alloy to BS1474 HE30TF, FC1 or 6262
 Cadmium per QQ-P-416, Type II, Class 3
 Over appropriate under plate,
 Per MIL-C-85049 (500 hour salt spray)
 Moulded Part Material: -100C (Black); Polyolefin/Silver Composites, semi-flexible
 ZEROHAL™ Low fire hazard
 Kits to include cleaning tissue, 1 piece 100 grit emery cloth & packing piece.
 Kit to be used in conjunction with installation guide for straight assemblies.

Dimensions in mm [inches for reference]

Part No.	Shell Size	B DIA MAX	D DIA MIN	J		P ±10% b	L REF a	JO REF b	JW ±30% b
				MIN a	MAX b				
KTKK0640	08	15.6 [.61]	6.3 [.25]	7 [.28]	5.0 [.20]	60 [2.36]	54 [2.13]	15 [.59]	1.0 [.04]
KTKK0641	10	18.6 [.73]	9.4 [.37]	9 [.35]	6.0 [.24]	75 [2.95]	69 [2.72]	17 [.67]	1.0 [.04]
KTKK0642	12	22.1 [.87]	12.9 [.51]	11 [.43]	7.2 [.28]	87 [3.43]	81 [3.19]	20 [.79]	1.0 [.04]
KTKK0643	14	26.1 [1.03]	14.2 [.56]	11 [.43]	7.2 [.28]	87 [3.43]	81 [3.19]	20 [.79]	1.0 [.04]
KTKK0644	16	29.6 [1.17]	18.9 [.74]	17 [.67]	8.5 [.33]	100 [3.94]	91 [3.58]	25 [.98]	1.0 [.04]
KTKK0645	18	33.1 [1.30]	18.9 [.74]	17 [.67]	8.5 [.33]	100 [3.94]	91 [3.58]	25 [.98]	1.0 [.04]
KTKK0646	20	36.1 [1.42]	23.7 [.93]	21 [.83]	10.0 [.39]	125 [4.92]	113 [4.45]	30 [1.18]	1.2 [.05]
KTKK0647	22	39.6 [1.56]	23.7 [.93]	21 [.83]	10.0 [.39]	125 [4.92]	113 [4.45]	30 [1.18]	1.2 [.05]
KTKK0648	24	42.6 [1.68]	31.4 [1.24]	29 [1.14]	15.8 [.62]	150 [5.91]	135 [5.31]	30 [1.18]	1.5 [.06]

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2016 By TE Connectivity

DIMENSIONS: mm [INCHES]	DWN P. VU	12OCT2016	MATERIAL	SEE NOTES	FINISH	SEE NOTES
	CHK N. NAGAR	12OCT2016	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. POPE	12OCT2016				
0 PLC ± -	PRODUCT SPEC	NAME ADAPTOR ASSEMBLY				
1 PLC ± -	—	—				
2 PLC ± -	APPLICATION SPEC	—				
3 PLC ± -	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
4 PLC ± -	—	A4	00779	C-KTKK0640-0648	—	
ANGLES ± -	WEIGHT	CUSTOMER DRAWING				
		SCALE	DNS	SHEET	1 OF 1	REV 6