



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

KAPTON LABELS OVERVIEW






SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
T1K	D08273-000	T1K-095095-10-9	KP228, Kapton white gloss (0,063 mm), Acrylic adhesive	TTDS-034
T2K	C63758-000	T2K-095095-10-9	KP842, Kapton white gloss (0,118 mm), Acrylic adhesive	TTDS-035
TSK	C18174-000	TSK-095095-10-9	KP7251, Kapton white gloss (0,118 mm), Acrylic adhesive	TTDS-085

Quantity per roll: 10.000 PCs
 Labels across: 7
 Winding: outside
 length of roll: 18,15 m



KAPTON SERIES

All dimensions in mm [inch]
 labels are centered on the liner
 as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity	
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,012]	 DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK S. Iser / 01.04.2020 DATE	 Name Kapton Label Size „095095“			
	ADHESIVE	LABEL WIDTH:	±0,3 [0,012]		APVD S. Iser / 01.04.2020 DATE				
	LINER	WEB WIDTH:	±0,8 [0,031]		PRODUCT SPEC DATE				
		VERTICAL REPEAT:	±0,8 [0,031]*		APPLICATION SPEC DATE				
		HORIZONTAL REPEAT:	±0,8 [0,031]*	WEIGHT T1K: 0,009 g T2K/TSK: 0,014g	SIZE A3	CAGE CODE C2290	DRAWING NO. C-KAPTON	RESTRICTED TO	
		PRINT POSITIONING:	±0,8 [0,031]*	MATERIAL SEE TABLE	FINISH GLOSS UNPRINTED MATT PRINTED	CUSTOMER DRAWING			
		LEFT MARGIN:	±0,4 [0,016]			SHEET 1 of 1			
		QUANTITY:	-0% +2%			REV A1			
		*NON ACCUMULATING							