



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI





# KAPTON LABELS OVERVIEW

SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
T1K	A81191-000	T1K-191064-10-9	KP228, Kapton white gloss (0,063 mm), Acrylic adhesive	TTDS-034
T2K	E84197-000	T2K-191064-10-9	KP842, Kapton white gloss (0,118 mm), Acrylic adhesive	TTDS-035
TSK	A61118-000	TSK-191064-10-9	KP7251, Kapton white gloss (0,118 mm), Acrylic adhesive	TTDS-085

Quantity per roll: 10.000 PCs  
 Labels across: 4  
 Winding: outside  
 length of roll: 23,82 m



All dimensions in mm [inch]  
 labels are centered on the liner  
 as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity			
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,12]	DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK S. Iser / 01.04.2020 DATE	APVD S. Iser / 01.04.2020 DATE	Name			
	ADHESIVE	LABEL WIDTH:	±0,3 [0,12]			Kapton Label Size „191064“					
	LINER	WEB WIDTH:	±0,8 [0,31]	 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	MATERIAL SEE TABLE	FINISH GLOSS UNPRINTED MATT PRINTED	PRODUCT SPEC DATE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		VERTICAL REPEAT:	±0,8 [0,31]*				APPLICATION SPEC DATE	A3	C2290	©-KAPTON	
		HORIZONTAL REPEAT:	±0,8 [0,31]*				WEIGHT				
		PRINT POSITIONING:	±0,8 [0,31]*				T1K: 0,009 g   T2K/TSK: 0,014g				
		LEFT MARGIN:	±0,4 [0,16]								
		QUANTITY:	-0% +2%								
		*NON ACCUMULATING									

KAPTON SERIES