



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
4		RELEASED AS PER ECO-17-009529	03JUL2017	PV	MP

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:

Raychem Connector Code: 40
 Connector Series: MIL-C-38999 SERIES 3 & 4
 208M7**-19C**-KNS (Bright);
 Adaptor Series: Aluminium Alloy to BS1474 HE30TF, FC1 or 6262
 Electroless Nickel per SAE-AMS-C-26074, Class 3 or 4, Grade B
 Or ASTM B-733, SC2, Type I, Class 5

Moulded Part Material: -100C (Black); Polyolefin/Silver Composites, semi-flexible
 ZEROHAL™ Low fire hazard

Kits to include cleaning tissue, 1 piece 100 grit emery cloth & packing piece.
 Kit to be used in conjunction with installation guide for straight assemblies.

Dimensions in mm [inches for reference]

Part No.	Shell Size	B DIA MAX	D DIA MIN	J		P ±10% b	L REF a	JO REF b	JW ±30% b
				MIN a	MAX b				
KTKK0670C	A	19.2 [.76]	6.2 [.24]	7 [.28]	5 [.2]	57 [2.24]	51 [2.01]	15 [.59]	1.0 [.04]
KTKK0671C	B	21.7 [.85]	9.3 [.37]	9 [.35]	6 [.24]	72 [2.83]	66 [2.6]	17 [.67]	1.0 [.04]
KTKK0672C	C	25.5 [1.0]	12.9 [.51]	11 [.43]	7.2 [.28]	84 [3.31]	78 [3.07]	20 [.79]	1.0 [.04]
KTKK0673C	D	29.3 [1.15]	14.1 [.56]	11 [.43]	7.2 [.28]	84 [3.31]	78 [3.07]	20 [.79]	1.0 [.04]
KTKK0674C	E	31.9 [1.26]	18.8 [.74]	17 [.67]	8.5 [.33]	97 [3.82]	88 [3.46]	25 [.98]	1.0 [.04]
KTKK0675C	F	35.7 [1.41]	18.8 [.74]	17 [.67]	8.5 [.33]	97 [3.82]	88 [3.46]	25 [.98]	1.0 [.04]
KTKK0676C	G	38.2 [1.5]	23.6 [.93]	21 [.83]	10 [.39]	122 [4.8]	110 [4.33]	30 [1.18]	1.2 [.05]
KTKK0677C	H	42.0 [1.65]	23.6 [.93]	21 [.83]	10 [.39]	122 [4.8]	110 [4.33]	30 [1.18]	1.2 [.05]
KTKK0678C	J	44.6 [1.76]	30.9 [1.22]	29 [1.14]	15.8 [.62]	147 [5.79]	132 [5.2]	30 [1.18]	1.5 [.06]

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. COPYRIGHT 2016 By TE Connectivity

DIMENSIONS:
mm [INCHES]

DWN P. VU 12OCT2016
 CHK N. NAGAR 12OCT2016

MATERIAL SEE NOTES

FINISH SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

APVD M. POPE 12OCT2016
 PRODUCT SPEC

NAME ADAPTOR ASSEMBLY



TE Connectivity

APPLICATION SPEC

SIZE A4 CAGE CODE 00779 DRAWING NO C-KTKK0670C-0678C

RESTRICTED TO

WEIGHT
 CUSTOMER DRAWING

SCALE DNS SHEET 1 OF 1 REV 4

