





LABEL AND LINER DESIGN

PRESENTATION

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23/11/2023	YB	AK



LABELS PER ROLL: 2 500
LABELS ACROSS: 1

OUTSIDE WOUND

TE PN: 7-1768814-3

All dimensions in mm [INCHES]


MATERIAL	CLEAR POLYESTER
ADHESIVE TYPE	PERMANENT
MATERIAL	SILVER POLYESTER
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	KRAFT WHITE

- Kiss cut
- Back slit
- Perforation
- 2 kiss cut enductions
- Die cut
- Adhesive cut
- 45° die cut

Grid removed: YES
Sales unit: THE LABEL

PRINTING		
	Color	Color
1	BLACK	5
2		6
3		7
4		8

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.3 [.012]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. BONINO 23NOV2023	 TE Connectivity			
DIMENSIONS: mm [inches]		CHK Y. BONINO 23NOV2023				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD A. KEAN 23NOV2023	NAME Part Description LBC-DBK-LA0024 -			
		PRODUCT SPEC -				
		APPLICATION SPEC -				
		WEIGHT -				
MATERIAL SEE TABLE			SIZE A2	CAGE CODE A00YM	DRAWING NO C=7-1768814-3	RESTRICTED TO -
			SCALE NTS	SHEET 1 OF 1	REV A	