



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	RELEASED AS PER ECO-17-009529	03JUL2017	PV	MP

a) Part as supplied.



b) Part after unrestricted recovery.



NOTES:

Raychem Connector Code: 76

Connector Series: BS 9522 F0017 (PATT 105)

Adaptor Series: 228M0**-19-B**-K-NS (Olive Drab);

Aluminium Alloy to BS1474 HE30TF, FC1 or 6262

Cadmium per QQ-P-416, Type II, Class 3

Over appropriate under plate,

Per MIL-C-85049 (500 hour salt spray)

Moulded Part Material:

-100C (Black); Polyolefin/Silver Composites, semi-flexible

ZEROHAL™ Low fire hazard

Kits to include cleaning tissue, 1 piece 100 grit emery cloth & packing piece.

Kit to be used in conjunction with installation guide for straight assemblies.

Dimensions in mm [inches for reference]

Part No.	Shell Size	B DIA MAX	D DIA MIN	J		P ±10% b	L REF a	JO REF b	JW ±30% b
				MIN a	MAX b				
KTKK0465A	08	17.1 [.67]	6.9 [.27]	9 [.35]	6.0 [.24]	78 [3.07]	72 [2.83]	17 [.67]	1.0 [.04]
KTKK0466A	10	20.1 [.79]	9.9 [.39]	11 [.43]	7.2 [.28]	90 [3.54]	84 [3.31]	20 [.79]	1.0 [.04]
KTKK0467A	12	23.6 [.93]	13.4 [.53]	17 [.67]	8.5 [.33]	103 [4.06]	94 [3.70]	25 [.98]	1.0 [.04]
KTKK0468A	14	26.6 [1.05]	16.4 [.65]	17 [.67]	8.5 [.33]	103 [4.06]	94 [3.70]	25 [.98]	1.0 [.04]
KTKK0469A	16	30.1 [1.19]	19.4 [.76]	21 [.83]	10.0 [.39]	128 [5.04]	116 [4.57]	30 [1.18]	1.2 [.05]
KTKK0470A	18	33.1 [1.30]	21.9 [.86]	21 [.83]	10.0 [.39]	128 [5.04]	116 [4.57]	30 [1.18]	1.2 [.05]
KTKK0471A	20	36.6 [1.44]	24.9 [.98]	29 [1.14]	15.8 [.62]	153 [6.02]	138 [5.43]	30 [1.18]	1.5 [.06]
KTKK0472A	22	39.6 [1.56]	28.4 [1.12]	29 [1.14]	15.8 [.62]	153 [6.02]	138 [5.43]	30 [1.18]	1.5 [.06]
KTKK0473A	24	43.1 [1.70]	30.9 [1.22]	37 [1.46]	16.8 [.66]	124 [4.88]	110 [4.33]	38 [1.50]	2.4 [0.09]

DIMENSIONS:

mm [INCHES]

DWN

P. VU

10OCT2016

MATERIAL

SEE NOTES

FINISH

SEE NOTES

CHK

N. NAGAR

10OCT2016

APVD

M. POPE

10OCT2016

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

CUSTOMER DRAWING

NAME

ADAPTOR ASSEMBLY

SIZE

A4

CAGE CODE

00779

DRAWING NO

C-KTKK0465A-0473A

RESTRICTED TO

—

SCALE

DNS

SHEET

1 OF 1

REV

3

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2016 By TE Connectivity

0 PLC ± —
 1 PLC ± —
 2 PLC ± —
 3 PLC ± —
 4 PLC ± —
 ANGLES ± —

