





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2018
 © COPYRIGHT2018 BY - TE Connectivity ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
G		ADDED DOV-12C AND DOV-25E	12JUN2020	RS	EFG
H		ADDED DOV-10B AND DOV-15C	22SEP2020	RS	EFG
J		REVISED	26APR2022	VF	EFG
K		REVISED	22JUL2022	VF	EFG



SIZE	No. SHEDS	CREEPAGE LENGTH (mm)	FLASHOVER DISTANCE (mm)	DIM L (mm)	DIM Ø S1 (mm)	DIM Ø S2 (mm)
A	6	405	162	160	105	93
B	11	697	234	229	105	93
C	13	817	266	258	105	93
D	15	945	304	298	105	93
E	15	1128	318	298	120	103

SIZE	PRODUCT (TEXT V)	Ur (TEXT W)	Uc (TEXT X)	APPROX. WEIGHT (kg)
A	DOV-03A	Ur 3.5 kV	Uc 2.8 kV	0.96
	DOV-04A	Ur 4.5 kV	Uc 3.6 kV	0.96
	DOV-05A	Ur 5 kV	Uc 4 kV	0.99
	DOV-06A	Ur 6 kV	Uc 4.8 kV	0.99
	DOV-09A	Ur 9 kV	Uc 7.2 kV	1.03
	DOV-10A	Ur 10.5 kV	Uc 8.4 kV	1.06
	DOV-12A	Ur 12 kV	Uc 9.6 kV	1.08
	DOV-13A	Ur 13.5 kV	Uc 10.8 kV	1.10
	DOV-15A	Ur 15 kV	Uc 12 kV	1.13
B	DOV-10B	Ur 10.5 kV	Uc 8.4 kV	1.46
	DOV-12B	Ur 12 kV	Uc 9.6 kV	1.48
	DOV-13B	Ur 13.5 kV	Uc 10.8 kV	1.50
	DOV-15B	Ur 15 kV	Uc 12 kV	1.53
	DOV-16B	Ur 16.5 kV	Uc 13.2 kV	1.55
	DOV-18B	Ur 18 kV	Uc 14.4 kV	1.57
	DOV-19B	Ur 19.5 kV	Uc 15.6 kV	1.60
	DOV-21B	Ur 21 kV	Uc 16.8 kV	1.62
	DOV-22B	Ur 22.5 kV	Uc 18 kV	1.64
	DOV-24B	Ur 24 kV	Uc 19.2 kV	1.66
DOV-25B	Ur 25.5 kV	Uc 20.4 kV	1.68	
C	DOV-12C	Ur 12 kV	Uc 9.6 kV	1.66
	DOV-15C	Ur 15 kV	Uc 12 kV	1.70
	DOV-18C	Ur 18 kV	Uc 14.4 kV	1.74
	DOV-21C	Ur 21 kV	Uc 16.8 kV	1.80
	DOV-22C	Ur 22.5 kV	Uc 18 kV	1.82
	DOV-24C	Ur 24 kV	Uc 19.2 kV	1.84
D	DOV-22D	Ur 22.5 kV	Uc 18 kV	2.04
	DOV-24D	Ur 24 kV	Uc 19.2 kV	2.06
	DOV-25D	Ur 25.5 kV	Uc 20.4 kV	2.08
	DOV-27D	Ur 27 kV	Uc 21.6 kV	2.10
	DOV-28D	Ur 28.5 kV	Uc 22.8 kV	2.13
	DOV-30D	Ur 30 kV	Uc 24 kV	2.15
E	DOV-25E	Ur 25.5 kV	Uc 20.4 kV	2.28
	DOV-30E	Ur 30 kV	Uc 24 kV	2.35
	DOV-31E	Ur 31.5 kV	Uc 25.2 kV	2.37
	DOV-33E	Ur 33 kV	Uc 26.4 kV	2.39
	DOV-34E	Ur 34 kV	Uc 27.2 kV	2.40
	DOV-36E	Ur 36 kV	Uc 28.8 kV	2.44



- NOTES:
- 1- REFER TO TECHNICAL DATASHEETS FOR ALL OTHER PRODUCT DETAILS
 - 2- ALUMINIUM END FITTINGS
 - 3- GREY SILICONE HOUSING
 - 4- HOUSING PRINT:

TE Logo
IEC 99-4
In 10 kA DH
Is 20 kA

ALL DIMENSIONS NOMINAL UNLESS SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15FEB2018 V.FUZZETTI	 TE Connectivity													
DIMENSIONS: mm		CHK 15FEB2018 E.F.GASTALDI														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 15FEB2018 S.A.KUMAR														
<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>± 0.5</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> <tr><td>FINISH</td><td>-</td></tr> </table>		0 PLC		±	1 PLC	±	2 PLC	±	3 PLC	± 0.5	4 PLC	±	ANGLES	±	FINISH	-
0 PLC	±															
1 PLC	±															
2 PLC	±															
3 PLC	± 0.5															
4 PLC	±															
ANGLES	±															
FINISH	-															
MATERIAL SEE NOTES	SEE DATASHEET	PRODUCT SPEC APPLICATION SPEC	SIZE A3													
CUSTOMER DRAWING		WEIGHT TABLE	CAGE CODE 00779													
SCALE NTS		DRAWING NO C-MV-DOV-01258-C	RESTRICTED TO -													
SHEET 1 OF 1		REV K														