



WITH ATTACHMENT



ATTACHMENT OPTIONS:



OMIT FOR NO ATTACHMENT
(SEE SHEET 2)

100P820S-16-1-C-WR4-03

SERIES _____
INSERT F FOR _____
FLUROSILICONE GASKET
OMIT FOR STANDARD
SILICONE GASKET
SHELL SIZE (TABLE 1) _____
MATERIAL (TABLE 5) _____
FINISH (TABLE 6) _____
LANYARD TYPE (TABLE 4) _____
LANYARD LENGTH (IN INCHES) _____
+1,0"/-0" TOLERANCE
ATTACHMENT (SEE ABOVE) _____

DRAWN	J.CLARK		DATE 29/05/2008	 3RD ANGLE PROJECTION NOT TO SCALE	 POLAMCO LTD www.polamco.com	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY	
SALES APPR		29/05/2008						
DESIGN APPR			UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°	ASSY USED ON: MIL-DTL-5015 REVERSE BAYONET / VG95234				
PROD APPR				TITLE: RECEPTACLE PROTECTION COVER				
QUAL APPR				MATERIAL SEE PART NUMBER BREAKDOWN	PART NUMBER: 100P820S SERIES		DRAWING NO: P10298	SHT 1
ISSUE 4	REV 2	DCR 3969						
NCAGE CODE U5792			WEIGHT	SEE PART NUMBER BREAKDOWN				

TABLE 1

SHELL SIZE	ØA MAX	B MAX	C MAX
10SL	23,3	22,5	15,90
12S	23,3	21,0	15,90
14S	29,6	22,5	15,90
16S	32,6	22,5	15,90
16	32,6	24,5	19,80
18	36,1	24,5	19,80
20	39,2	24,5	19,80
22	42,7	24,5	19,80
24	46,4	24,5	19,80
28	52,0	24,5	19,80
32	58,7	24,5	19,80
36	64,9	24,5	19,80
40	70,7	24,5	19,80

TABLE 2

EYELET REF.	ØF
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

TABLE 3

RING REF.	ØE
10	16,1
12	19,4
14	22,6
16	25,8
18	27,8
20	30,6
22	34,1
24	36,9
28	44,6
32	51,2
36	57,5

TABLE 4

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

TABLE 5

CODE	MATERIAL
1	ALUMINIUM
2	NICKEL ALUMINIUM BRONZE
4	STAINLESS STEEL


LIST NOT EXHAUSTIVE, SEE MATERIAL TABLE
FOR OTHER OPTIONS

TABLE 6


CODE	DESCRIPTION
B	CADMIUM, OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
G	BLACK ANODISE, SULPHURIC
J	PASSIVATE
U	UNPLATED CLEAN FINISH NOT SHOT BLASTED
Z	SHOT BLAST FOR NON-REFLECTIVE FINISH
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, SEE PLATING TABLE FOR OTHER OPTIONS

WITHOUT ATTACHMENT



100P820S-16-1-C
NO ATTACHMENT VERSION
SIMILAR TO M83723/60-2**AN



100P820S-16-1-C-EO
EYELET ONLY VERSION
(NO LANYARD)

DRAWN	J.CLARK	DATE	29/05/2008	3RD ANGLE PROJECTION NOT TO SCALE	POLAMCO LTD www.polamco.com	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.
SALES APPR		29/05/2008					
DESIGN APPR				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	ASSY USED ON: MIL-DTL-5015 REVERSE BAYONET / VG95234 RECEPTACLE		
PROD APPR					TITLE:	RECEPTACLE PROTECTION COVER	
QUAL APPR				MATERIAL SEE PART NUMBER BREAKDOWN	PART NUMBER:	100P820S SERIES	DRAWING NO: SHT
ISSUE	REV	DCR	3969	FINISH SEE PART NUMBER BREAKDOWN			P10298 2
NCAGE CODE U5792	WEIGHT						