








PART MARK AND BATCH CODE
"MM96-xx-x-x Pxxxxxx"


**SL - (SHORT)
SLOTTED HEAD SCREW**



**E - EXTENDED
SLOTTED HEAD SCREW**



**FSK - FLOATING
SOCKET HEAD SCREW**



MM96-25X-1-C-SL

SERIES
SHELL SIZE (TABLE 1)
X - SILICONE PADS OMITTED
MATERIAL AND PLATING
HARDWARE OPTION:
(SL - (SHORT) SLOTTED HEAD SCREW)
(E - EXTENDED SLOTTED HEAD SCREW)
(EK - EXTENDED SOCKET HEAD SCREW)
(FSK - FLOATING SOCKET HEAD SCREW)
(OMIT FOR STANDARD (SHORT) SOCKET HEAD SCREW)

Table 1							
SHELL SIZE	A	B	C	D	E	F	G THREAD
09	19,70	9,00	14,35	17,30	8,90	7,00	2-56 UNC
15	23,40	9,00	18,16	19,30	10,90	7,00	2-56 UNC
21	27,30	9,00	21,97	21,00	12,60	7,00	2-56 UNC
25	29,85	9,00	24,51	22,70	14,30	7,00	2-56 UNC
31	33,70	9,00	28,32	24,20	15,80	7,00	2-56 UNC
37	37,50	9,00	32,13	25,60	17,20	7,00	2-56 UNC
51	36,14	10,00	30,86	24,40	16,00	8,00	2-56 UNC
100	54,90	11,00	45,72	36,80	28,40	10,00	4-40 UNC

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZB	ALUMINIUM / ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
1-Y	ALUMINIUM / YELLOW CHROMATE OVER CADMIUM
4-J	STAINLESS STEEL / PASSIVATE

DRAWN	DIW	DATE 24/04/2017		PART NUMBER: MM96 SERIES		 Polamco connectivity
SALES APPR				TITLE: MICRO MIN STRAIN RELIEF BACKSHELL ASSEMBLY		
DESIGN APPR			UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°	ASSY USED ON: MIL-DTL-83513		
PROD APPR				THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		
QUAL APPR			MATERIAL SEE PART NUMBER BREAKDOWN	POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 1	DRAWING NO: P14768
ISSUE AA	REV.	DCR CRN26424	FINISH SEE PART NUMBER BREAKDOWN			
NCAGE CODE U5792		WEIGHT				