



ANGLE 1



ANGLE 2



ANGLE 3

TABLE 1

SHELL SIZE	A THREAD	ØB MAX	ØG MIN	ØH MAX	C ± 0,5	D MAX	E MAX	F MAX	K ±0,5	RECOMMENDED BOOTSIZE
09	M12x1.0	18,0	6,8	13,5	13,1	17,6	25,7	25,5	17,5	202 K 121
11	M15x1.0	21,0	9,9	15,4	13,9	18,4	26,7	27,3	17,5	202 K 121
13	M18x1.0	24,5	13,6	19,7	14,5	19,3	31,2	28,7	20,0	202 K 142
15	M22x1.0	29,0	15,9	21,3	15,5	19,6	37,2	30,2	24,5	202 K 142
17	M25x1.0	32,5	18,9	24,5	16,1	20,4	40,2	31,9	26,7	202 K 153
19	M28x1.0	35,5	21,9	26,5	16,8	20,8	44,7	33,5	27,0	202 K 153
21	M31x1.0	37,0	25,2	31,0	17,1	21,6	49,2	35,1	30,5	202 K 153
23	M34x1.0	40,0	27,4	34,4	17,7	22,5	51,7	36,7	31,5	202 K 163
25	M37x1.0	43,5	30,4	36,6	18,4	22,9	53,2	38,1	28,5	202 K 163

TABLE 2

CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, SEE PLATING TABLE FOR OTHER OPTIONS

97H1-17-1-C-ET

SERIES \_\_\_\_\_  
 CONNECTOR INTERFACE \_\_\_\_\_  
 ANGLE \_\_\_\_\_  
 SHELL SIZE (TABLE 1) \_\_\_\_\_  
 MATERIAL \_\_\_\_\_  
 ALUMINIUM ALLOY  
 FINISH (TABLE 2) \_\_\_\_\_  
 EARTH TAG \_\_\_\_\_

DRAWN	K.WINCZURA	DATE	18/04/2013	3RD ANGLE PROJECTION NOT TO SCALE
SALES APPR			18/04/2013	
DESIGN APPR	K.SHEPPARD	DATE	07/08/2013	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 1°
PROD APPR				
QUAL APPR				<b>MATERIAL</b> SEE PART NUMBER BREAKDOWN  <b>FINISH</b> SEE PART NUMBER BREAKDOWN
ISSUE	3	DCR	6245	
NCAGE CODE U5792		WEIGHT	---	



**POLAMCO LTD**  
 www.polamco.com

WESTON LOCK  
 LOWER BRISTOL ROAD  
 BATH BA2 1EP

ASSY USED ON: MIL-DTL-38999 SERIES III & IV

TITLE:  
 HEAT SHRINK BOOT BACKSHELL WITH EARTH TAG

PART NUMBER:  
 97H-ET SERIES

THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

DRAWING NO: P25870  
 SHT 1