

KIT COMPRISES:
HEATSHRINK BOOT
MAGNAFORM ADAPTOR 70MMTB-U-**-**-1-
(SUPPLIED WITH LOCKING HARDWARE)

TABLE 1

SHELL SIZE	A	B	C	D
09	19,70	14,35	9,0	11,0
15	23,40	18,16	9,0	11,0
21	27,30	21,97	9,0	11,0
25	29,85	24,51	9,0	15,0
31	33,70	28,32	9,0	15,0
37	37,50	32,13	9,0	20,0
51	36,10	30,86	10,0	20,0


TABLE 2

ENTRY SIZE	G MAX
04	3,2
05	4,0
06	4,8
07	5,6
08	6,4

TABLE 3

CODE	PLATING
C	ELECTROLESS NICKEL AMS-C-26074 CLASS 4 GRADE B
M	BRIGHT CADMIUM OVER NICKEL QQ-P-416 TYPE II CLASS 3
Y	YELLOW CHROMATE OVER CADMIUM QQ-P-416 TYPE II CLASS 2

*NOTE:
'DIMENSIONS ONLY APPLY AFTER UNRESTRICTED RECOVERY - THE PART IS
SUPPLIED WITH THE BOOT IN AN UN-RECOVERED STATE'



100P2554-15-08-1-C
SERIES
SHELL SIZE (SEE TABLE 1)
ENTRY SIZE (SEE TABLE 2)
MATERIAL (1 - ALUMINIUM ALLOY)
PLATING (TABLE 3)

AB	CRN 26424	N.HAWKINS	26/09/24
AA	CRN 26424	N.HAWKINS	22/07/24
2	DCR 5635	K.K-W	09/12/13
ISS / REV	DESCRIPTION	CHANGED BY	DATE

MATERIAL/FINISH
SEE ROUTE CARD
FOR MATERIAL

FINISH ALLOWANCE
PER SURFACE
ALUM ALLOY 0.025
ST STEEL 0.00
ALUM BRONZE 0.00
DIMENSIONS APPLY
AFTER PLATING

3RD ANGLE
PROJECTION
NOT TO SCALE

REMOVE ALL SHARP
EDGES AND BURRS
UNLESS OTHERWISE
SPECIFIED
ALL DIMENSIONS IN
MILLIMETRES
GENERAL TOL
LINEAR +/-0.1MM
ANGULAR +/- 1°
FILLET RADII 0,40MM MAX




POLAMCO

TITLE
MIRCO MIN MAGNAFORM
ADAPTOR ASSEMBLY AND
HEATSHRINK BOOT KIT

THIS DRAWING IS COPYRIGHTANDTHE PROPERTY OF TE CONNECTIVITY
IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE
DISCLOSED WITHOUT PRIORWRITTEN CONSENT OF THE COMPANY.

PART NO
100P2554-**-**-1-*

DRAWN	K.SHEPPARD	DATE	15/01/2009
DESIGN APPR	M.PAUL		15/09/2009
PROD APPR	K.SMITH		15/09/2009
QUAL APPR	P.REES		15/09/2009
REV AB	DRG NO P9122		



<