


REVISIONS



R85049/128-1

SERIES \_\_\_\_\_  
 SIZE \_\_\_\_\_

SEE TABLE 1 FOR TWO-STEP BAND DESCRIPTION  
 SEE TABLE 2 FOR ONE-STEP BAND DESCRIPTION

NOTES:

1. THE BAND STRAPS ARE CONSTRUCTED FROM 300 SERIES PASSIVATED CORROSION RESISTING STEEL.
2. THE PRODUCT SHALL BE IDENTIFIED ON THE PACKAGE LABEL.
3. PART MARKING:  
 ONE STEP BAND STRAP WILL BE PERMANENTLY MARKED WITH TE LOGO.  
 TWO STEP BAND STRAP WILL BE PERMANENTLY MARKED WITH TE LOGO.
4. RECOMMENDED INSTALLATION TOOLS AS PER TABLE 1 FOR TWO -STEP BAND &  
 TABLE 2 FOR ONE-STEP BAND
5. THE INSTALLATION TOOL FOR ONE STEP BAND AND TWO STEP BAND ARE NOT INTERCHANGEABLE.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT 20 BY

DIMENSIONS: INCHES	DWN: K.KUTA-WINCZURA 05/07/2019	MATERIAL: STAINLESS STEEL	FINISH: PASSIVATE	
	CHK: R.STYLES 11/12/2019	<b>STE</b> TE Connectivity		
TOLERANCES UNLESS OTHERWISE SPECIFIED:  GENERAL TOL LINEAR .XX - ±0.03" .XXX - ±0.015" ANGULAR ±1°	APVD: M.PAUL 11/12/2019	PART NUMBER: R85049/128-*		
	PRODUCT SPEC: -	NAME: SCREEN TERMINATION BAND		
APPLICATION SPEC: -	WEIGHT:	SIZE: A4	CAGE CODE: U5792	DRAWING NO: C-P35607
	CUSTOMER DRAWING	RESTRICTED TO	SCALE: 1:5	SHEET: 1 OF 3
				REV: AD

REVISIONS

R85049/128-1 - FLAT  
R85049/128-2 - PRE-COILED  
TWO-STEP STANDARD BAND

M85049/128-5 - FLAT  
M85049/128-6 - PRE-COILED  
TWO-STEP MICRO BAND






TABLE 1

PART NUMBER	A	B ±.030 (0,75)	C ±.010 (0,25)	D ±.003 (0,08)	E ±.015 (0,38)	G MAX	H REF	TOOL REQ.
R85049/128-1	13.94 (354,08) 14.31 (363,47)	.328 (8,33)	.245 (6,22)	.019 (0,48)	.100 (2,54)	-	-	M81306/2-01
R85049/128-2	-	-	-	-	-	.140 (3,56)	1.750 (44,45)	M81306/2-01
R85049/128-5	9.44 (239,77) 9.56 (242,82)	.198 (5,03)	.118 (3,00)	.015 (0,38)	.080 (2,03)	-	-	M81306/2-02
R85049/128-6	-	-	-	-	-	.120 (3,05)	1.12 (28,45)	M81306/2-02

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

BY COPYRIGHT 20

DIMENSIONS:  
INCHES

DWN: K.KUTA-WINCZURA 05/07/2019

MATERIAL: STAINLESS STEEL

FINISH: PASSIVATE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

CHK: R.STYLES 11/12/2019



GENERAL TOL  
LINEAR  
.XX ±.003"  
.XXX ±.0015"  
ANGULAR ±1°

APVD: M.PAUL 11/12/2019

PART NUMBER: R85049/128-\*

PRODUCT SPEC:


NAME: SCREEN TERMINATION BAND

APPLICATION SPEC:

SIZE CAGE CODE DRAWING NO RESTRICTED TO

WEIGHT:

A4 U5792 C=P35607



CUSTOMER DRAWING

SCALE 1:5 SHEET 2 OF 3 REV AD

REVISIONS

R85049/128-3- FLAT  
R85049/128-4 - PRE-COILED  
ONE-STEP STANDARD BAND

R85049/128-7 - FLAT  
R85049/128-8 - PRE-COILED  
ONE-STEP MICRO BAND





TABLE 2

PART NUMBER	A	B ±.030 (0.75)	C ±.010 (0.25)	D ±.003 (0.08)	E ±.015 (0.38)	F REF	G MAX	H REF	TOOL REQ.
R85049/128-3	14.19 (360,42) 14.31 (363,47)	.350 (8,89)	.245 (6,22)	.019 (0,48)	.074 (1,88)	2.031 (51,59)	-	-	M81306/1-01
R85049/128-4	-	-	-	-	-	-	.150 (3,81)	1.750 (44,45)	M81306/1-01
R85049/128-7	8.06 (204,72) 8.18 (207,77)	.195 (4,95)	.115 (2,92)	.015 (0,38)	.053 (1,35)	2.031 (51,59)	-	-	M81306/1-02
R85049/128-8	-	-	-	-	-	-	.073 (1,85)	1.12 (28,45)	M81306/1-02

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 20 BY

DIMENSIONS:  
INCHES

DWN: K.KUTA-WINCZURA 05/07/2019

MATERIAL: STAINLESS STEEL

FINISH: PASSIVATE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

CHK: R.STYLES 11/12/2019



GENERAL TOL  
LINEAR  
.XX ±.003"  
.XXX ±.015"  
ANGULAR ±1°

APVD: M.PAUL 11/12/2019

PART NUMBER: R85049/128-\*

PRODUCT SPEC:

NAME: SCREEN TERMINATION BAND

APPLICATION SPEC:

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A4	06090	Ⓒ-P35607	

WEIGHT:  
Customer Drawing

SCALE 1:5 SHEET 3 OF 3 REV AD

