


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	25MAR2024	AN	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED						AS RECOVERED							
	EXPANDED I.D. (D)						MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS (W)					
	MINIMUM		NOMINAL		MAXIMUM				MINIMUM		NOMINAL		MAXIMUM	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
RNF-100-1.3MM	1.09	0.043	1.30	0.051	1.50	0.059	0.41	0.016	-	-	-	-	0.38	0.015

PRODUCT INFORMATION

- 1 FLAME RETARDANT
- 2 MATERIAL: IRRADIATED MODIFIED POLYOLEFIN
STANDARD COLOUR: CLEAR
- 3 LONGITUDINAL CHANGE 0 TO -10%
- 4 TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED
FROM THE PRODUCT SIZES REFERENCED WITHIN THIS
DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN 25MAR2024
AYESHABANU N

CHK 25MAR2024
BASAVARAJA D A

APVD 25MAR2024
VLADIMIR NEMEC

PRODUCT SPEC
RT-350

APPLICATION SPEC
114-120022

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
RNF-100-1.3MM

SIZE
A3

CAGE CODE
-

DRAWING NO
RNF-100-1.3MM

RESTRICTED TO
-

SCALE
NTS

SHEET
1

OF
1

REV
A