

Α4

U5792

~−P35877

SCALE

1:5


SHEET

 \Box F

AA

WEIGHT:

CUSTOMER DRAWING





ONE STEP BAND STRAP - STRAIGHT

PART NUMBER	ENTRY SIZE	A ±1,8 [±.071]	B ±1,0 [±.040]	C ±0,2 [±.010]	D REF.	E REF.
BND-0812S	03 TO 12	206,3 [8.120]	5,0 [.197]	2,9 [.114]	0,4 [.016]	1,8 [.071]
BND-1412S	03 TO 24	362,0 [14.252]	5,0 [.197]	2,9 [.114]	0,4 [.016]	1,8 [.071]
BND-1425S	03 TO 24	362,1 [14.260]	8,9 [.350]	6,2 [.244]	0,5 [.020]	1,9 [.075]

TWO STEP BAND STRAP - STRAIGHT

1770 0121 27 112 0110 11 0110 110111						
PART NUMBER	ENTRY SIZE	A ±1,8 [±.071]	B ±1,0 [±.040]	C ±0,2 [±.010]	D REF.	E REF.
BND-1012S	03 TO 12	241,0 [9.488]	5,1 [.201]	3,0 [.118]	0,4 [.016]	2,2 [.087]
BND-1225S	ND-1225S 03 TO 24		8,3 [.327]	6,2 [.244]	0,5 [.020]	2,5 [.098]
BND-1212S	03 TO 24	362,0 [14.252]	5,0 [.197]	3,0 [.118]	0,5 [.020]	2,5 [.098]






ONE STEP BAND STRAP - PRE-COILED

PART NUMBER	ENTRY SIZE	ØA REF
BND-0812P	03 TO 12	28,5 [1.120]
BND-1412P	03 TO 24	44,5 [1.752]
BND-1425P	03 TO 24	44,5 [1.752]

TWO STEP BAND STRAP - PRE-COILED

PART NUMBER	ENTRY SIZE	ØA REF
BND-1012P	03 TO 12	28,5 [1.120]
BND-1225P	03 TO 24	44,5 [1.752]
BND-1212P	03 TO 24	44,5 [1.752]



В

20

COPYRIGHT

						REVISIONS		
			PART NUMBER	DESCRIPTION	BAND SLOT WIDTH (MM)	VISUALISATION		
D FOR PUBLICATION			M81306/1-02	PRE-CALIBRATED HAND TOOL FOR ONE STEP MICRO BAND BND-0812S BND-0812P BND-1412S BND-1412P	3,18	CUT-OFF HANDLE TENSION RELEASE LEVER BAND SLOT TOOL BODY CUT-OFF BLADE PULL-UP HANDLE GRIPPER RELEASE HANDLE		
			M81306/1-01	PRE-CALIBRATED HAND TOOL FOR ONE STEP STANDARD BANDS BND-1425S BND-1425P	6,35	CUT-OFF HANDLE TENSION RELEASE LEVER TOOL BODY CUT-OFF BLADE PULL-UP HANDLE GRIPPER RELEASE HANDLE		
RELEASED	ALL RIGHTS RESERVED.	RIGHTS	M81306/2-02 INCLUDES: - TIGHTENING TOOL - M81306/2-02B - FOLDING TOOL - M81306/2-02D	PRE-CALIBRATED HAND TOOL FOR TWO STEP BAND BND-1012S BND-1012P BND-1212S BND-1212P	3,18	TIGHTENING TOOL M81306/2-02B CUT OFF HANDLE FOLDING TOOL M81306/2-02D BAND SLOT & CUT OFF MECHANISM PULL UP HANDLE		
THIS DRAWING IS UNPUBLISHED.	C COPYRIGHT 20 BY	INCLUDES: - TIGHTENING TOOL - M81306/2-01A - FOLDING TOOL -		PRE-CALIBRATED HAND TOOL FOR TWO STEP BAND BND-1225S BND-1225P	6,65	TIGHTENING TOOL M81306/2-01A CUT OFF HANDLE FOLDING TOOL M81306/2-02D BAND SLOT & CUT OFF MECHANISM		
Ė	DIMENSIONS: MILLIMETERS DWN: K.KUTA-WINCZURA 26/11/2019		1/2019 MATERI	AL: 300 SERIES CORROSION FINISH: PASSIVATED				
\vdash	TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL TOL LINEAR 10,25MM ANGULAR 11.		ANCES UNLESS	APVD: M.PAUL 11/12/2019 PA		PART NUMBER: BND-XXXXX NAME: SCREEN TERMIANTION BAND		
			ERAL TOL AR <u>+</u> 0,25MM JULAR <u>+</u> 1°					
			APPLICATION SPEC:		SIZE	CAGE CODE DRAWING NO RESTRICTED TO		
	⊕ ← →		- WEIGHT:		 ∆4	U5792 C-P35877		
				CUSTOMER DRAWING	3	SCALE 1:5 SHEET 3 OF 3 REV AA		