

	Component Dimensions					Cable Dimensions				
Product Name	Ident.	L±1.75	Н	ØВ	ØС	ØD	ØΕ	ØF	ØG	
	Code	(L±0.07)	min	min	min	max	max	min	max	
S02-17-R-XX	SZ2A26	16.50	8.25	2.65	3.68	2.65	3.68	1.40	0.72	
		(0.650)	(0.325)	(0.105)	(0.145)	(0.105)	(0.145)	(0.055)	(0.030)	
S02-18-R-XX	SZ3A26	16.50	8.25	4.30	5.08	4.30	5.08	2.15	1.25	
		(0.650)	(0.325)	(0.170)	(0.200)	(0.170)	(0.200)	(0.085)	(0.050)	
S02-20-R-XX	SZ5A26	19.10	8.25	7.00	7.60	7.00	7.60	4.30	2.50	
		(0.750)	(0.325)	(0.275)	(0.300)	(0.275)	(0.300)	(0.170)	(0.100)	

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn63 per ANSI J-STD-006.

FLUX: TYPE ROL1 per ANSI-J-STD-004.

THERMAL INDICATOR: Color change violet to colorless.


- 3. SEALING RINGS: Environment resistant thermoplastic. Color: blue.
- 4. PRE-INSTALLED LEAD: RAYCHEM 55A0111-26-XX* in accordance with MIL-W-22759/32-26-XX*

*XX: Part name and lead callout shall be replaced with lead color designation per MIL-STD-681.

Colors available: solid and with single stripe.

APPLICATION

- 1. These parts are designed to provide an environment protected shield termination on cables, rated for 105°C minimum, meeting the dimensional criteria listed and having tin or silver plated shields and insulation compatible with the insert material. For compatible insulations, consult TE Connectivity.
- 2. When installed per Raychem process standard RCPS-100-70, assemblies will meet those requirements of Raychem Specification RT-1404.
- 3. For assembly information, refer to Raychem document RCPS-100-70.
- 4. Parts shall be marked with identification code per table.
- 5. For best results, prepare the cable as shown:
 - Strip length of shield: 6.35 8.25 (0.250 0.325)
 - Use methods (a) or (b) with cable rated for 125°C and above. Use method (c) for cables rated for 105°C and cable with spiral wrapped shields.



Raychem THERMOFIT DEVICES				SOLDERSLEEVE* SHEILD TREMINATION ENVIRONMENT RESISTANT WITH LEAD					
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]					DOCUMENT NO.: S02-17/-18/-20-R-XX				
TOLERANCES:	ROUGHNESS IN MICRON		TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.						
0.00 N/A 0.0 N/A 0 N/A					REV:		DATE: 27OCT2023		
DRAWN BY: DATE: D. MALLIKA 19NOV20		021	ECN: ECN-23-234831	SCALE: NTS		SIZE: A	SHEET: 1 of 1		

© 2022 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

^{*}TE Connectivity, TE connectivity (logo), Raychem, Thermofit, SolderSleeve are trademarks