
CUSTOMER DRAWING



	Component Dimensions					Shall Accommodate		
				Cable with Dimensions				
Product Name	Ident.	L±1.75	ØВ	ØC	Н	ØΕ	ØF	ØD
	Code	(L±0.07)	min	min	min	max	min	max
S03-01-R-9035	1-HB	16.5	1.9	2.65	8.25	2.65	0.90	1.9
		(0.650)	(0.075)	(0.105)	(0.325)	(0.105)	(0.035)	(0.075)
S03-02-R-9035	2-HB	16.5	2.65	3.68	8.25	3.68	1.40	2.65
		(0.650)	(0.105)	(0.145)	(0.325)	(0.145)	(0.055)	(0.105)
S03-03-R-9035	3-HB	16.5	4.3	5.08	8.25	5.08	2.15	4.3
		(0.650)	(0.170)	(0.200)	(0.325)	(0.195)	(0.085)	(0.170)
S03-04-R-9035	4-HB	19.1	5.95	6.45	8.25	6.45	3.30	5.95
		(0.750)	(0.235)	(0.255)	(0.325)	(0.255)	(0.130)	(0.235)
S03-05-R-9035	5-HB	19.1	7.0	7.6	8.25	7.6	4.30	7.0
		(0.750)	(0.275)	(0.300)	(0.325)	(0.300)	(0.170)	(0.275)

MATERIAL

1. INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyvinylidene fluoride. Transparent blue.

2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn63 per ANSI J-STD-006.

FLUX: TYPE ROL1 per ANSI J-STD-004.

THERMAL INDICATOR: Color change violet to colorless.

3. MELTABLE RINGS: Thermally stabilized thermoplastic. Color: blue.

4. PRE-INSTALLED BRAID: Tin plated copper strands. CMA 1000.

APPLICATION


1. These parts are designed to provide an environment protected shield termination on cables, rated for 125°C minimum, meeting the dimensional criteria listed and having tin or silver plated shields and insulation compatible with the insert material. For compatible insulations, see MIL-S-83519/2 or consult TE Connectivity.

2. When installed per Raychem process standard RCPS-100-70, assemblies will meet those requirements of Raychem Specification RT-1404 and MIL-S-83519/2 which do not require electrical testing while parts are immersed in water.

3. Temperature range: -55°C to +175°C.

4. Parts shall be marked with identification code per table.

For best results, prepare the cable as shown:



Raychem THERMOFIT DEVICES				TITLE: SOLDERSLEEVE* DEVICE SHIELD TERMINATION WITH BRAID					
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]				DOCUMENT NO.: S03-0X-R-9035					
TOLERANCES: 0.00 N/A	ANGLI			onnectivity reserves the right to d this drawing at any time.	REV :		DATE :		
0.0 N/A 0 N/A	ROUG MICRO	HNESS IN DN	Users should evaluate the suita of the product for their applicat		REV:		30-Mar-2020		
DRAWN BY: DATE: M. FORONDA 19-Jan-9		99	ECO: ECO-20-004510	SCALE: NTS		SIZE: A	SHEET: 1 of 1		

© 2020 TE Connectivity Ltd. Family of Companies. All Rights Reserved.

If this document is printed it becomes uncontrolled. Check for the latest revision.

*TE Connectivity, TE connectivity (logo), Raychem, THERMOFIT, SolderSleeve are trademarks