



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REDRAWN IN CREO	08NOV2023	AN	VN

PART AS SUPPLIED

PART FULLY RECOVERED



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED							
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		WALL THICKNESS (W)					
	mm.	in.	mm.	in.	MINIMUM		MAXIMUM		NOMINAL	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
3/64	1.17	.046	0.58	.023	0.33	.013	0.48	.019	0.40	.016
1/16	1.60	.063	0.79	.031	0.35	.014	0.50	.020	0.43	.017
3/32	2.36	.093	1.17	.046	0.43	.017	0.58	.023	0.50	.020
1/8	3.17	.125	1.57	.062	0.43	.017	0.58	.023	0.50	.020
3/16	4.74	.187	2.36	.093	0.43	.017	0.58	.023	0.50	.020
1/4	6.35	.250	3.17	.125	0.56	.022	0.71	.028	0.64	.025
3/8	9.50	.374	4.74	.187	0.56	.022	0.71	.028	0.64	.025
1/2	12.70	.500	6.35	.250	0.56	.022	0.71	.028	0.64	.025
3/4	19.05	.750	9.50	.374	0.69	.027	0.84	.033	0.76	.030
1	25.40	1.000	12.70	.500	0.76	.030	1.01	.040	0.88	.035
1-1/4	31.75	1.250	15.88	.625	0.86	.034	1.17	.046	1.01	.040
1-1/2	38.10	1.500	19.05	.750	0.86	.034	1.17	.046	1.01	.040
2	50.80	2.000	25.40	1.000	0.96	.038	1.32	.052	1.14	.045
3	76.20	3.000	38.10	1.500	1.06	.042	1.47	.058	1.27	.050
4	101.60	4.000	50.80	2.000	1.16	.046	1.63	.064	1.39	.055
5	127.00	5.000	63.50	2.500	1.30	.051	1.75	.069	1.52	.060


PRODUCT INFORMATION

1. FLAME RETARDANT
2. MATERIAL: IRRADIATED MODIFIED POLYOLEFIN  
STANDARD COLOURS: BLACK, WHITE, RED, BLUE, YELLOW, CLEAR  
NON-STANDARD COLOUR: BROWN, ORANGE, GREEN, VIOLET, GREY
3. SHRINK RATIO 2:1
4. LONGITUDINAL CHANGE 0 TO -5%
5. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm




TOLERANCES UNLESS OTHERWISE SPECIFIED:  
0 PLC ±.1  
1 PLC ±0.1  
2 PLC ±0.01  
3 PLC ±0.001  
4 PLC ±0.0001  
ANGLES ±  
FINISH -

MATERIAL

SEE NOTE

DWN	08NOV2023
CHK	AYESHABANU N
APVD	08NOV2023
APVD	BASAVARAJA D A
APVD	09NOV2023
APVD	VLADIMIR NEMEC
PRODUCT SPEC	RT-350
APPLICATION SPEC	114-120022
WEIGHT	-
CUSTOMER DRAWING	



NAME  
RNF-100-IRRADIATED MODIFIED POLYOLEFIN SINGLE WALL HEAT SHRINK TUBING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	© RNF-100_USA_STANDARD_SIZES	-
SCALE	SHEET	OF	REV
NTS	1	1	A1