

PRODUCT DIMENSIONS

	AS SUPPLIED		AS RECOVERED				
SIZE NUMBER	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. (d)		TOTAL WALL THICKNESS AFTER RECOVERY (W)		
501 V	mm.	in.	mm.	in.	mm.	in.	
50I-X	10.50	0.4 3	1.8	0.071	1.8	0.071	

PRODUCT INFORMATION

- I. NON-FLAME RETARDANT
- 2. OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN TYPE COLOUR: CLEAR INNER LINER: POLYAMIDE HOT MELT ADHESIVE COLOUR: LIGHT AMBER
- 3. FULL RECOVERED LONGITUDINAL SHRINKAGE: -5 TO -15%
- 4. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)			CONTROLLED DOCUMENT.	DWN 12JUN2023				
	CUT LENGTH	TOLERANCE	- THIS DRAWING IS A	CONTROLLED DOCUMENT.	BASAVARAJA DA CHK		TE Conne	ectivity
	UPTO TO 9.90mm	\pm l.50mm	DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED	SELVAPANDIAN B			
	IOmm TO 24.90mm	\pm l.50mm	mm(lnches)	OTHERWISE SPECIFIED.	MAYO BAKARE	T KFFW		
	25mm TO 54.90mm	\pm l.50mm		0 PLC ±-	RK-6214	DUAL WALL	SLEEVING	
	55mm TO 99.90mm	\pm 3.00mm		2 PLC ±0.0 3 PLC ±0.001	APPLICATION SPEC	-		
	100mm TO 149.90mm	\pm 4.00mm		4 PLC ±0.0001 ANGLES ±-	_	SIZE CAGE CODE DRA		RESTRICTED TO
	150mm TO 499.90mm	\pm 5.00mm	SEE NOTE	FINISH -	WEIGHT _	A3 - C	C = RPPMNR.50I - X	-
	500mm AND GREATER	\pm 25.40mm		-	CUSTOMER DRAWING		scale NTS sheet	^{of} ^{rev} A

|470-|9 (3/|3)

С

В

REVISIONS			
DESCRIPTION	DATE	DWN	APVD
SE	12JUN2023	BDA	MB

В

С