
CUSTOMER DRAWING



Product		Product Dimensions				Cable Dimensions		
Name	Ident	L±1.75	øB	øС	Н	øΕ	øF	øD
	Code	(L±0.075)	min	min	min	max	min	max
SO96-1-55-22-95	SO961R	16.5	1.90	2.67	8.20	2.67	0.90	1.90
		(0.650)	(0.075)	(0.105)	(0.322)	(0.105)	(0.035)	(0.075)
SO96-2-55-22-95	SO962R	16.5	2.67	3.68	8.20	3.68	1.40	2.67
		(0.650)	(0.105)	(0.145)	(0.322)	(0.145)	(0.055)	(0.105)
SO96-3-55-22-95	SO963R	16.5	4.32	5.08	8.20	5.08	2.15	4.32
		(0.650)	(0.170)	(0.200)	(0.322)	(0.200)	(0.085)	(0.170)
SO96-4-55-22-95	SO964R	19.1	5.97	6.48	8.20	6.48	3.30	5.97
		(0.750)	(0.235)	(0.255)	(0.322)	(0.255)	(0.130)	(0.235)
SO96-5-55-22-95	SO965R	19.1	6.98	7.62	8.20	7.62	4.30	6.98
		(0.750)	(0.275)	(0.300)	(0.322)	(0.300)	(0.170)	(0.275)

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn96 per ANSI-J-STD-006.

FLUX: TYPE ROM1 per ANSI-J-STD-004.


THERMAL INDICATOR: Color change orange to colorless.

- 3. MELTABLE RINGS: Environment resistant thermoplastic. Color: blue.
- 4. PRE-INSTALLED LEAD: Raychem 55A0813-22-95 in accordance with MIL-W-22759/41-22-95 AWG22 stranded nickel plated copper. Color: white with green stripe.

APPLICATION

- 1. These parts are designed to an environment resistant shield termination on cables, rated for 150°C minimum, meeting the dimensional criteria listed, having nickel-plated shields and insulations compatible with the insert material. See MIL-S-83519/1 or consult Raychem.
- 2. Temperature range: -55°C to +175°C.
- 3. Parts shall be marked with identification code per table.
- 4. Install using TE Connectivity-approved convection or infra-red heating tools in accordance with Raychem Process Standard RCPS-100-70. Infrared tools are not recommended for use with black jackets.

For best results, prepare the wire as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

<i>=<u>™</u></i>			THE	<i>aychem</i> ERMOFIT EVICES		TLE: SOLDERSLEEVE DEVICE SHIELD TERMINATION WITH LEADS, HIGH TEMPERATURE IMMERSION RESISTANT					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.						DOCUMENT NO.: SO96-X-55-22-95					
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ROUGHNESS IN this draw evaluate t		this drawing at any tin	ectivity reserves the right to amend ring at any time. Users should the suitability of the product for lication.		Revision: A		Issue Date: April 2020			
DRAWN BY: DATE: M. FORONDA 06-Jan-		6: 06-Jan-00	ECO: ECO-20-004961		SCALE: None	SIZE: A	SHEET: 1 of 1				