



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION MAR , 2017.
 © COPYRIGHT 2017 By TE Connectivity ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	22MAR2017	GK	DB
	F	LINER CHANGE	12SEP2018	GK	DB

LABEL AND LINER DESIGN

PRESENTATION



OUTSIDE WOUND LABEL ACROSS: 2 PER ROLL QTY: 1000

All dimensions in mm [Inch]

TE PN: CN9931-000

MATERIAL	CLEAR VINYL
ADHESIVE TYPE	ACRYLIC PERMANENT
LINEAR	WHITE KRAFT

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22MAR2017	
LABEL HEIGHT:	± 0.3 [.012]	DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC \pm - 4 PLC \pm - ANGLES \pm - FINISH \pm -		GK	
LABEL WIDTH:	± 0.3 [.012]			GK	
WEB WIDTH:	± 0.8 [.031]			GK	
VERTICAL REPEAT:	± 0.8 [.031]*			GK	
HORIZONTAL REPEAT:	± 0.8 [.031]*	GK		GK	
PRINT POSITIONING:	± 0.8 [.031]*	GK		GK	
LEFT MARGIN:	± 0.4 [.016]	GK		GK	
QUANTITY:	-0 % +2 % *NON ACCUMULATING	GK		GK	

UL-MARKING AND LABELLING SYSTEMS		
PGIS2 - Marking and Labeling Systems, Limited Use - Component (UL 969)		
File: MH61871	Product design: SBP	Ribbon: TMS-XXX-RIBBON-4RPSCE

DWN 22MAR2017		GK	
CHK 22MAR2017		GK	
APVD 22MAR2017		GK	
D.BURGAT		GK	
D.BURGAT		GK	
PRODUCT SPEC TTDS-211		GK	
APPLICATION SPEC		GK	
WEIGHT 1.013g		GK	
SIZE A2	CAGE CODE 00779	DRAWING NO. SBP190594WE1	RESTRICTED TO
CUSTOMER DRAWING		SCALE NTS	SHEET 1 of 1
		REV F	