


REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE NPR 9051	93-08-02	Kohlman

SALES DRAWING

REVISION STATUS OF SHEETS																	
REV.	A	A	A	A	A	A	A	A	A	A	A	A					
SHEET	1	2	3	4	5	6	7	8	9	10	11	12					

REV. STATUS OF SHEETS								P.O. BOX 4422 Santa Barbara, CA 93140-4422	
REV.						TITLE GENERAL PURPOSE AEROSPACE 270VDC, 10A VACUUM RELAY		DWG. NO. AP10B SERIES	
SHEET									
REV.									
SHEET									
PREP. BY	TANNER	93-07-23	CAGE CODE 18741		SHEET 1 OF 12				
CHKD. BY	Kohlman	93-08-02							
ENG. APRVL	Kohlman	93-08-02							

REV.

A

SPECIFICATIONS:

PHYSICAL

CONTACT ARRANGEMENT	SPST-NC
FORM	B

ENVIRONMENTAL

SHOCK, 11 MS 1/2 SINE (g, Peak)	50
VIBRATION, SINUSOIDAL (55-2000 Hz; g PEAK)	10
OPERATING TEMPERATURE (°C)	-55 TO +85
OPERATIONAL ALTITUDE, MAX. (FT.)	80,000

ELECTRICAL

CONTACT RATING	
OPERATING VOLTAGE (Vdc)	270
RATED RESISTIVE LOAD @ 270 VDC (Amps)	10*
LOAD LIFE, MIN. (CYCLES)**	7,000
OVERLOAD, SWITCHED (Adc)	20
OVERLOAD CONTACT LIFE, MIN (CYCLES)	50
CONTINUOUS CURRENT CARRY, MAX. (Adc)	SEE TABLE I

TABLE I	ADC
AP10B232, AP10B234, AP10B332, AP10B334, AP10B532, AP10B534 AP10B732, AP10B734, AP10B832, AP10B834, AP10B932, AP10B934 AP10BA57, AP10BB57, AP10BC57	15
AP10B235, AP10B245, AP10B335, AP10B345, AP10B535, AP10B545, AP10BA47, AP10BB47, AP10BC47	10

OTHER DATA

DIELECTRIC STRENGTH AT SEA LEVEL (VRMS)	
COIL TO CASE	500
ALL OTHER POINTS	2,000
DIELECTRIC STRENGTH AT 80,000 FT. ALL POINTS (VRMS)	500
OPERATE TIME, MAX., INCLUDING BOUNCE AT NOMINAL VOLTAGE (ms)	10
RELEASE TIME, MAX. (ms)	10
INSULATION RESISTANCE, 500 Vdc, MIN. (MEGOHMS)	
BEFORE LIFE	100
AFTER LIFE	50
CONTACT RESISTANCE, MAX. (OHMS)	SEE TABLE II

TABLE II	OHMS
AP10B232, AP10B234, AP10B332, AP10B334, AP10B532, AP10B534 AP10B732, AP10B734, AP10B832, AP10B834, AP10B932, AP10B934 AP10BA57, AP10BB57, AP10BC57	.010
AP10B235, AP10B245, AP10B335, AP10B345, AP10B535, AP10B545 AP10BA47, AP10BB47, AP10BC47	.030

COIL DATA

COIL VOLTAGE, NOMINAL (Vdc)	12	28	120
COIL VOLTAGE, MAX. (Vdc)	14	32	140
PICK-UP VOLTAGE, MAX. (Vdc)	10	20	85
DROP-OUT VOLTAGE, (Vdc)	.3-6	.7-12	5-55
COIL RESISTANCE (OHMS $\pm 10\%$ @ 25°C)	53	290	4700

NOTES: RATINGS LISTED ARE ACROSS THE OPERATING TEMPERATURE RANGE.

*THE LOAD TERMINALS SHOULD ALWAYS BE CONNECTED AS FOLLOWS: COMMON CONTACT +; OTHER CONTACT -.

**USING WEIBULL RELIABILITY AT 95%. SEE ALSO LOAD LIFE GRAPH ON SHEET 4.

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$.xxx = $\pm .010$ $\angle x^\circ = \pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
NONE

SHEET
2

PART NUMBER SELECTION

SAMPLE PART NUMBER: AP10 B B 5 7

CONTACT FORM: B = SPST-NC

COIL OPTIONS

- 2 = 12 Vdc - BUS WIRE/PC BOARD (SEE FIGURES 1, 2, 5 & 6)
- 3 = 28 Vdc - BUS WIRE/PC BOARD (SEE FIGURES 1, 2, 5 & 6)
- 5 = 120 Vdc - BUS WIRE/PC BOARD (SEE FIGURES 1, 2, 5 & 6)
- 7 = 12 Vdc - TURRET TERMINAL (SEE FIGURES 3 & 4)
- 8 = 28 Vdc - TURRET TERMINAL (SEE FIGURES 3 & 4)
- 9 = 120 Vdc - TURRET TERMINAL (SEE FIGURES 3 & 4)
- A = 12 Vdc - STUD TERMINAL (SEE FIGURE 7 & 8)
- B = 28 Vdc - STUD TERMINAL (SEE FIGURE 7 & 8)
- C = 120 Vdc - STUD TERMINAL (SEE FIGURE 7 & 8)

POWER TERMINAL OPTIONS

- 3 = SOLDER CONNECTION/PC BOARD (SEE FIGURES 1-5)
- 4 = FLYING LEAD (SEE FIGURES 6 & 7)
- 5 = STUD TERMINAL (SEE FIGURE 8)

MOUNTING OPTIONS

- 2 = FLANGED MOUNT (SEE FIGURES 1 & 3)
- 4 = THROUGH CHASSIS MOUNT (SEE FIGURES 2 & 4)
- 5 = PC BOARD MOUNT (SEE FIGURES 5 & 6)
- 7 = PANEL MOUNT (SEE FIGURE 7 & 8)

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE

18741


SCALE

NONE

SHEET

3


SCHEMATIC
(FOR FIGURES 1-4, 7 & 8 ONLY)



NOTE: ON PANEL MOUNT OPTIONS, COIL TERMINALS ARE POLARIZED AS FOLLOWS: X1 IS NEGATIVE (-), X2 IS POSITIVE (+).

AP10B

Failure Rate vs. Rated Resistive Load Life at 10 A, 270 Vdc



* Failure Rate letter designations per MIL-STD-690

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation


P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
NONE

SHEET
4



WEIGHT, MAX (oz): 1.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
2 = 12 Vdc - BUS WIRE LEADS 3 = 28 Vdc - BUS WIRE LEADS 5 = 120 Vdc - BUS WIRE LEADS	3 = SOLDER CONNECTIONS	2 = FLANGED MOUNT

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 1: FLANGED STYLE MOUNTING WITH SOLDER TYPE POWER TERMINALS AND BUS WIRE COIL LEADS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation


P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
1:1

SHEET
5



WEIGHT, MAX (oz): 1.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
2 = 12 Vdc - BUS WIRE LEADS 3 = 28 Vdc - BUS WIRE LEADS 5 = 120 Vdc - BUS WIRE LEADS	3 = SOLDER CONNECTIONS	4 = THROUGH CHASSIS MOUNT

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 2: THROUGH CHASSIS STYLE MOUNTING WITH SOLDER TYPE POWER TERMINALS AND BUS WIRE COIL LEADS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = \pm .03

.xxx = \pm .010

\angle x° = \pm 2°

DO NOT SCALE DWG.

Kilovac[®]
Corporation


P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
1:1

SHEET
6



WEIGHT, MAX (oz): 1.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
7 = 12 Vdc - TURRET TERMINALS 8 = 28 Vdc - TURRET TERMINALS 9 = 120 Vdc - TURRET TERMINALS	3 = SOLDER CONNECTIONS	2 = FLANGED MOUNT

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 3: FLANGED STYLE MOUNTING WITH SOLDER TYPE POWER TERMINALS AND TURRET COIL TERMINALS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation


P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
1:1

SHEET
7



WEIGHT, MAX (oz): 1.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
7 = 12 Vdc - TURRET TERMINALS	3 = SOLDER CONNECTIONS	4 = THROUGH CHASSIS MOUNT
8 = 28 Vdc - TURRET TERMINALS		
9 = 120 Vdc - TURRET TERMINALS		

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 4: THROUGH CHASSIS STYLE MOUNTING WITH SOLDER TYPE POWER TERMINALS AND TURRET COIL TERMINALS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = \pm .03

.xxx = \pm .010

\angle x° = \pm 2°

DO NOT SCALE DWG.

Kilovac[®]
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422


AP10B SERIES

CAGE CODE
18741


SCALE
1:1

SHEET
8

SCHEMATIC



*HARDWARE MARKING
WILL BE AS SHOWN
IN PARENTHESES.



WEIGHT, MAX (oz): 2.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
2 = 12 Vdc - PCB TERMINALS	3 = PCB TERMINALS	5 = PCB MOUNT
3 = 28 Vdc - PCB TERMINALS		
5 = 120 Vdc - PCB TERMINALS		

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 5: PC BOARD STYLE MOUNTING WITH PC BOARD TERMINALS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac[®]
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422


AP10B SERIES

CAGE CODE
18741

SCALE
1:1

SHEET
9

SCHEMATIC



*HARDWARE MARKING WILL BE AS SHOWN IN PARENTHESES.

NOTES:

1. TERMINALS 1 AND 2 ARE FOR MOUNTING ONLY, THEY ARE NOT ELECTRICALLY CONNECTED.


WEIGHT, MAX (oz): 2.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
2 = 12 Vdc - PCB TERMINALS 3 = 28 Vdc - PCB TERMINALS 5 = 120 Vdc - PCB TERMINALS	4 = FLYING LEADS	5 = PCB MOUNT

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 6: PC BOARD STYLE MOUNTING FLYING POWER LEADS



DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac
Corporation


P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES


CAGE CODE
18741

SCALE
1:1

SHEET
10



2X #4(.112)-40 UNC-2A (EACH WITH
HEX NUT, LOCKWASHER & FLAT WASHER)
TORQUE (MAX): 4.4 LB-IN



WEIGHT, MAX (oz): 2.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
A = 12 Vdc - STUD TERMINALS B = 28 Vdc - STUD TERMINALS C = 125 Vdc - STUD TERMINALS	4 = FLYING LEADS	7 = PANEL MOUNT

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 7: PANEL STYLE MOUNTING WITH FLYING POWER LEADS
AND STUD COIL TERMINALS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422


AP10B SERIES

CAGE CODE
18741

SCALE
1:1


SHEET
11

REV.
A



2X #4(.112)-40 UNC-2A (EACH WITH
HEX NUT, LOCKWASHER & FLAT WASHER)
TORQUE (MAX): 4.4 LB-IN

2X #6(.138)-32 UNC-2A (EACH WITH
HEX NUT, LOCKWASHER & FLAT WASHER)
TORQUE (MAX): 10 LB-IN



WEIGHT, MAX (oz): 2.00

AVAILABLE OPTIONS:

COIL OPTIONS	POWER TERMINAL OPTIONS	MOUNTING OPTIONS
A = 12 Vdc - STUD TERMINALS	5 = STUD TERMINALS	7 = PANEL MOUNT
B = 28 Vdc - STUD TERMINALS		
C = 125 Vdc - STUD TERMINALS		

(PART NUMBER, CONTACT RATINGS, COIL VOLTAGE/RESISTANCE AND SCHEMATIC ARE MARKED ON SIDES OF RELAY.)

FIGURE 8: PANEL STYLE MOUNTING WITH STUD TERMINALS

DIMENSIONS IN INCHES
(DIMENSIONS IN PARENTHESES ARE IN
MILLIMETERS)

TOLERANCES EXCEPT AS NOTED

.xx = $\pm .03$

.xxx = $\pm .010$

\angle x° = $\pm 2^\circ$

DO NOT SCALE DWG.

Kilovac
Corporation

P.O. BOX 4422
Santa Barbara, CA 93140-4422

AP10B SERIES

CAGE CODE
18741

SCALE
1:1

SHEET
12