
## **CUSTOMER DRAWING**



		Ų	0	0			0	
Product Revision		Tilant	Product Dimensions			Cable Dimensions		
Product		Ident. Code	L±1.75	øB	øC	øD	øE	øF
Name			(L±0.070)	min	min	max	max	min
SO175-1-01	А	SO1751R	16.50	1.90	2.67	1.90	2.67	0.90
			(0.650)	(0.075)	(0.105)	(0.075)	(0.105)	(0.035)
SO175-2-01	А	SO1752R	16.50	2.67	3.68	2.67	3.68	1.40
			(0.650)	(0.105)	(0.145)	(0.105)	(0.145)	(0.055)
SO175-3-01	А	SO1753R	16.50	4.32	5.08	4.32	5.08	2.15
			(0.650)	(0.170)	(0.200)	(0.170)	(0.200)	(0.085)
SO175-4-01	А	SO1754R	19.10	5.97	6.48	5.97	6.48	3.30
			(0.750)	(0.235)	(0.255)	(0.235)	(0.255)	(0.130)
SO175-5-01	А	SO1755R	19.10	6.98	7.62	6.98	7.62	4.30
			(0.750)	(0.275)	(0.300)	(0.275)	(0.300)	(0.170)

## MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.

2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:

SOLDER: TYPE Sn96 per ANSI/J-STD-006.

FLUX: TYPE ROM1 per ANSI/J-STD-004.


THERMAL INDICATOR: Fusible ring, melt point: 232°C, completely melted at 240°C.

3. MELTABLE SEALING RINGS: Thermally stabilized thermoplastic. Color: blue.

4. PRE-INSTALLED BRAID: Nickel-plated copper strands per ASTM B355 Class 7. CMA 640.

## APPLICATION

- 1. These parts are designed to provide an environment protected shield termination on cables, rated for 150°C minimum, meeting the dimensional criteria listed, having nickel-plated shields.
- Install using Raychem-approved convection or infrared heating tools in accordance with Raychem process standard RCPS-100-70. Infrared tools are not recommended for use with black jackets.
- 3. Parts shall be marked with identification code per table.
- 4. Temperature range: -55°C to +175°C.
- For best results, prepare the cable as shown:



SolderSleeve is a trademark of TE Connectivity Corporation.

© 2004-2018 TE Connectivity Corporation. All rights reserved

TE Connectivity						<b>Raychem</b> Devices	TITLE: SOLDERSLEEVE SHIELD TERMINATOR WITH PRE-INSTALLED BRAID, 175°C, LEAD-FREE			
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]						DOCUMENT NO.: SO175-X-01				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ROU	GLES: N/A JGHNESS IN RON	this d the su	to Electronics reserves the right to amend drawing at any time. Users should evaluate suitability of the product for their lication.			PROD. REV.: SEE TABLE	DOC. ISSUE: B	DATE: 24-SEPT-2018	
DRAWN BY: M. FOROND	A	CAGE CODE 06090	:	REPLACES: None		0 NUMBER: 20-18-014431	SCALE: None	SIZE: A	SHEET: 1 of 1	

If this document is printed it becomes uncontrolled. Check for the latest revision.