
CUSTOMER DRAWING



Product	Ident. Code	Produ	ct Dimensi	ons	Cable Dimensions			
Name		L±1.75	øB	øC	øD	øE	øF	øG
		(L±0.070)	min	min	max	max	min	min
SO63-1-W2-24-00-100	SO631R	16.50	1.90	2.65	1.90	2.65	0.90	0.50
5005-1-₩2-24-00-100	50051K	(0.650)	(0.075)	(0.105)	(0.075)	(0.105)	(0.035)	(0.020)
SO63-2-W2-24-00-100	SO632R	16.50	2.65	3.68	2.65	3.68	1.40	0.75
5005-2-112-24-00-100		(0.650)	(0.105)	(0.145)	(0.105)	(0.145)	(0.055)	(0.030)
SO63-3-W2-24-00-100	SO633R	16.50	4.30	5.08	4.30	5.08	2.15	1.25
3003-3-W2-24-00-100		(0.650)	(0.170)	(0.200)	(0.170)	(0.200)	(0.085)	(0.050)
SO63-4-W2-24-00-100	SO634R	19.10	5.95	6.45	5.95	6.45	3.30	1.80
3003-4-W2-24-00-100		(0.750)	(0.235)	(0.255)	(0.235)	(0.255)	(0.130)	(0.070)
SO63-5-W2-24-00-100	SO635R	19.10	7.00	7.60	7.00	7.60	4.30	2.50
5005-5- 12-24-00-100	50055K	(0.750)	(0.275)	(0.300)	(0.275)	(0.300)	(0.170)	(0.100)

MATERIALS


- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:
- SOLDER:TYPESn63 perANSI-J-STD-006.FLUX:TYPEROL1 perANSI-J-STD-004.

THERMAL INDICATOR: Fusible ring, melt point: 221°C.

- 3. MELTABLE RING: Environment resistant thermoplastic. Color: blue.
- 4. GROUND LEAD: Un-insulated Stranded Silver-plated Copper in accordance with Boeing 5M2409 Specification, AWG 24.

APPLICATION

- 1. These parts will provide a shield termination assembly when installed in accordance to Raychem RCPS-100-70 on cables rated for at least 125°C, meeting the dimensional criteria listed, having tin or silver plated shields.
- 2. Temperature rating: -55°C to +150°C.
- 3. Parts shall be marked with identification code per table. For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, and SolderSleeve are trademarks

E TE Raych			Raychem		TITLE: SOLDERSLEEVE SHIELD TERMINATOR ENVIRONMENT RESISTANT WITH LEAD					
Unless otherwise specified dimensions are in millimeters. Inches dimensions are in between brackets.					DOCUMENT NO.: SO63-X-W2-24-00-100					
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: ANGLES	this drawing at any time. User vESS IN evaluate the suitability of the p		ne. Users should	l	Revision: 2		Issue Date: March 2020		
PREPARED BY: DA mforonda		DAT	E: 9-Oct-02	ECO: ECO-2		0-004480	SCALE: None	SIZE: A	SHEET: 1 of 1	

Print Date: 2-Apr-20 If this document is printed it becomes uncontrolled. Check for the latest revision.