




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	29NOV2017	YC	CW
	AI	ECR-19-008112	23MAY2019	CD	CW



M3 SCREW
RECOMMENDED TIGHTENING
TORQUE 0.5N.m
M3 螺丝
推荐锁紧力矩0.5N.m

M4 SCREW
RECOMMENDED TIGHTENING
TORQUE 1.5N.m
M4 螺丝
推荐锁紧力矩1.5N.m



NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
表面处理: 见表格
防护等级: IP68(配合)

T1922036120-000	H3APR-TGC-M20	H3APR HOOD,CENTER LOCKING, TOP ENTRY M20, POWDER COATED, SILVER GREY H3APR 上壳, 中部锁定, 顶出M20, 银灰色粉末喷涂	M20X1.5	14
T1926030120-000	H3APR-TGC-M20	H3APR HOOD,CENTER LOCKING, TOP ENTRY M20, POWDER COATED, BLACK H3APR 上壳, 中部锁定, 顶出M20, 黑色粉末喷涂	M20X1.5	14
T1926030116-000	H3APR-TGC-M16	H3APR HOOD,CENTER LOCKING, TOP ENTRY M16, POWDER COATED, BLACK H3APR 上壳, 中部锁定, 顶出M16, 黑色粉末喷涂	M16X1.5	5
PART NUMBER 料号	PART DESCRIPTION 描述	THREAD PG/M 螺纹 PG/M	THREAD H 螺纹长度 H	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YORK CHEN 29NOV2017	TE Connectivity	
DIMENSIONS: mm		CHK GINO YAO 29NOV2017		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 29NOV2017		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-137011		
MATERIAL -		APPLICATION SPEC 114-137011	NAME H3APR-TGC-PG/M	
FINISH -		WEIGHT -	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 1:1	DRAWING NO C-T192603X1XX000	RESTRICTED TO -
		SHEET 1	OF 1	REV AI