

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	19JAN2019	WQR	CW
	AI	ECR-24-205194	24APR2024	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: SPCC
BODY SURFACE: ZINC PLATED

2. WIRE RANGE: SEE TABLE.




3. OBSOLETE

注释:


1. 技术参数:
主体材料: 冷轧板
主体表面处理: 镀锌

2. 夹线范围: 见表格.

3. 料号停用



MODEL MARK
型号标示



3	T1970667000-000	BK70	CABLE CLAMP BK70, 64-70mm 电缆夹子BK70, 64-70mm	75.5	44.0	100.0	Ø70	Ø64-Ø70	BK70
3	T1964566400-000	BK64	CABLE CLAMP BK64, 60-64mm 电缆夹子BK64, 60-64mm	69.5	44.0	103.0	Ø64	Ø60-Ø64	BK64
3	T1954465400-000	BK54	CABLE CLAMP BK54, 46-54mm 电缆夹子BK54, 46-54mm	61.0	44.0	84.0	Ø54	Ø46-Ø54	BK54
3	T1950425000-000	BK50	CABLE CLAMP BK50, 42-50mm 电缆夹子BK50, 42-50mm	57.0	44.0	80.0	Ø50	Ø42-Ø50	BK50
3	T1942384200-000	BK42	CABLE CLAMP BK42, 38-42mm 电缆夹子BK42, 38-42mm	48.0	39.5	72.0	Ø42	Ø38-Ø42	BK42
3	T1938303800-000	BK38	CABLE CLAMP BK38, 34-38mm 电缆夹子BK38, 34-38mm	45.0	39.5	68.0	Ø38	Ø34-Ø38	BK38
3	T1934303400-000	BK34	CABLE CLAMP BK34, 30-34mm 电缆夹子BK34, 30-34mm	41.0	39.5	64.0	Ø34	Ø30-Ø34	BK34
3	T1932263200-000	BK32	CABLE CLAMP BK32, 26-32mm 电缆夹子BK32, 26-32mm	40.0	39.5	60.0	Ø34	Ø26-Ø32	BK32
3	T1926222600-000	BK26	CABLE CLAMP BK26, 22-26mm 电缆夹子BK26, 22-26mm	31.5	39.5	52.0	Ø25.4	Ø22-Ø26	BK26
3	T1922182200-000	BK22	CABLE CLAMP BK22, 18-22mm 电缆夹子BK22, 18-22mm	26.5	39.5	46.5	Ø20	Ø18-Ø22	BK22
	T1918121800-000	BK18	CABLE CLAMP BK18, 14-18mm 电缆夹子BK18, 14-18mm	21.0	39.5	41.0	Ø18	Ø14-Ø18	BK18
	T1918121400-000	BK14	CABLE CLAMP BK14, 12-14mm 电缆夹子BK14, 12-14mm	20.0	39.5	33.4	Ø13	Ø12-Ø14	BK14
PART NUMBER 料号		DESCRIPTION 描述		W	WI	H	ØD (mm)	WIRE RANGE 夹线范围 (Ø)mm	MODEL MARK 型号标示

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN
WENQING RAO
19JAN2019

CHK
GINO YAO
19JAN2019

APVD
CHRIS WANG
19JAN2019

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
BK14/18/22/26/32/34/38/42
/50/54/64/70

SIZE
A3

CAGE CODE
-

DRAWING NO
C-T19XXXXXX00000

RESTRICTED TO

SCALE
1:1

SHEET
1

OF
1

REV
AI