

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	06NOV2017	RL	CW
	B1	ECR-17-017888	14DEC2017	RL	CW

M4 SCREW RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4 螺丝推荐扭力矩为 1.2Nm

PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS
不装壳体的面板安装开孔尺寸

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SCREW CONTACT

注释:

1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (20-14 AWG)
端子表面处理: 镀银
接线类型: 螺丝连接

T2010322201-001	HA-016-F 17-32	HA-016 FEMALE INSERT, 17-32, NO LOGO HA-016母插, 17-32, 无LOGO
-----------------	----------------	--

PART NUMBER
料号

PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 06NOV2017
ROY LIU
CHK 06NOV2017
GINO YAO
APVD 06NOV2017
CHRIS WANG

NAME
HA-016-F 17-32

STE TE Connectivity

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

FINISH

PRODUCT SPEC
108-137045APPLICATION SPEC
114-137045

WEIGHT

-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A3 00779 © T2010322201001

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV B1

1470-19 (3/13)