

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	23AUG2017	YC	CW
	B	ECR-22-150866	23SEP2022	DL	CW

SCALE 1:2

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

M4 SCREW
RECOMMENDED TIGHTENING TORQUE 1.2N.m
M4螺丝, 推荐拧紧力矩1.2N.m

4X M3 SCREW
RECOMMENDED TIGHTENING TORQUE 0.5N.m
4X M3螺丝, 推荐拧紧力矩0.5N.m

注释:

- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
- 端子需要单独订购,
(订货号参考图面: T20200X10XX000)

PANEL CUT OUT FOR INSERTS FOR USING
WITHOUT HOODS/HOUSINGS
不使用防护外壳时平面开孔尺寸

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
-	-
-	-

DWN	23AUG2017
YORK CHEN	
CHK	23AUG2017
GINO YAO	
APVD	23AUG2017
CHRIS WANG	
PRODUCT SPEC	108-137043
APPLICATION SPEC	114-137043
WEIGHT	-
CUSTOMER DRAWING	

T2031082101-007	HDD-108-M	HDD-108 MALE INSERT HDD-108 公插
PART NUMBER 料号	PART DESCRIPTION 产品描述	
STE TE Connectivity		
NAME HDD-108-M		
SIZE A3	CAGE CODE -	DRAWING NO T2031082101007
RESTRICTED TO		
SCALE 1:1	SHEET 1 OF 1	REV B

1470-19 (3/13)