


А	s Supplie	d	As Recovered							
	Inside Diameter 'D'		Inside Diameter 'd'		Wall Thickness 'W'					
Size	Minimum		Maximum		Minimum		Maximum		Nominal	
	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.
2.9/1.7	.114	2.89	.067	1.70	.019	0.48	.059	1.49	.039	0.99
4.0/2.9	.157	4.00	.114	2.89	.019	0.48	.059	1.49	.039	0.99
7.8/4.6	.307	7.79	.181	4.59	.019	0.48	.059	1.49	.039	0.99
10/6.5	.394	10.00	.256	6.49	.039	0.99	.079	2.00	.059	1.49
15/9.6	.591	15.01	.378	9.59	.039	0.99	.079	2.00	.059	1.49
21/13	.827	21.00	.511	12.99	.049	1.24	.109	2.76	.079	2.00
29/20	1.141	28.99	.787	19.99	.049	1.24	.109	2.76	.079	2.00
41/27	1.614	40.99	1.063	26.99	.079	2.00	.157	3.98	.118	2.99
51/33	2.007	50.99	1.299	32.99	.079	2.00	.157	3.98	.118	2.99

NOTES

- 1. THIS PRODUCT IS DESIGNED FOR A WIDE RANGE OF APPLICATIONS AND MEETS THE REQUIREMENTS OF TE SPECIFICATIONS RT-1142.
- 2. PACKAGED AND SUPPLIED ON A SPOOL. LABELED WITH PART NUMBER: SRFR= PRODUCT FAMILY, -2.9/1.7= ORDER SIZE, -0= BLACK (STANDARD COLOR). PACKAGING= -SP (SPOOL), Example: SRFR-2.9/1.7-0-SP.
- 3. ALWAYS ORDER THE LARGEST SIZE THAT WILL FIT SNUGGLY OVER THE COMPONENT TO BE COVERED.
- 4. FOR MATERIAL AND FINISH INFORMATION, REFER TO TE SPECIFICATION RT-1142. FOR SPECIAL ORDER SIZES, CONTACT TE CONNECTIVITY.

Raychem Harness & Components CUSTOMER DRAWING



© 2018-2020 TE Connectivity Corporation. All rights reserved.