

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	16NOV2017	RL	CW
	B1	ECR-17-017888	15DEC2017	RL	CW

NOTES:

- I. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SPRING CLAMP

注释:




- I. 技术参数:
绝缘材料: PC
额定电压: 500V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: $0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)
端子表面处理: 镀银
接线类型: 弹片压接




PANEL CUT OUT FOR INSERTS FOR
USE WITHOUT HOODS/HOUSING
不使用防护外壳时芯件的安装开孔图

M4 SCREW, RECOMMENDED TIGHTENING TORQUE 1.2Nm
M4 螺丝, 推荐扭力矩为 1.2Nm


4X M3 SCREW RECOMMENDED TIGHTENING TORQUE 0.5Nm
4 X M3螺丝, 推荐扭力矩为 0.5Nm



SCALE 3:5



T2040163101-002	HE-016-MS	HE-016 MALE INSERT, SPRING CLAMP, NO LOGO HE-016公插, 弹片, 无LOGO
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16NOV2017 ROY LIU	 TE Connectivity		
		CHK 16NOV2017 GINO YAO			
		APVD 16NOV2017 CHRIS WANG			
		PRODUCT SPEC 108-137044			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HE-016-MS		
		0 PLC ±-	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		1 PLC ±-			
		2 PLC ±-			
		3 PLC ±-			
		4 PLC ±-	A300779 © T2040163101002		
		ANGLES ±-			
MATERIAL		FINISH	SCALE 1:1 SHEET 1 OF 1 REV B1		
			CUSTOMER DRAWING		