





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	-
© COPYRIGHT copyright.d87e-	ALL RIGHTS RESERVED.	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	24NOV2016	DW	CW
	B	ECR-21-106515	21JUL2021	SQ	CW



PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING, ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm




M4 SCREW, RECOMMENDED —
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

注释：

- 技术参数：
绝缘材料：PC
额定电压：500V
额定电流：16A
绝缘电阻： $>=400M\Omega$
脉冲电压：6KV
污染等级：3
阻燃等级：UL94V-0
插拔次数：500次
接线范围：0.5mm²~2.5mm²（AWG20-AWG14）
端子表面处理：镀银
接线类型：双弹片连接

T2040245201-000		HE-024-FSS		HE-024 FEMALE INSERT, DOUBLE SPRING CLAMP HE-024母插, 双弹片	
PART NUMBER 料号		PART DESCRIPTION 描述			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24NOV2016 DAVID WANG CHK 24NOV2016 CHRIS WANG APVD 24NOV2016 XIANG XU PRODUCT SPEC 108-137044 APPLICATION SPEC 114-137044		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME HE-024-FSS	
MATERIAL		FINISH		SIZE A2	
-		-		CAGE CODE -	
-		-		DRAWING NO C=T2040245201000	
		WEIGHT -		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 1 REV B	