





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	04SEP2018	GY	CW
	B	ECR-20-008190	07AUG2020	WQR	CW
	B1	ECR-21-105138	29JUN2021	WQR	CW

NOTES:
I. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: CONDUCTIVE PAINTING
DEGREE OF PROTECTION: IP65 (MATED)

1. 技术参数：

上壳材料：	铝合金
表面处理：	喷导电漆
防护等级：	IP65（配合）



T1240165121-000	H16B-TGH-EMC-PG21	H16B EMC HOOD, TOP ENTRY PG21, 4 EAR, HIGH CONSTRUCTION H16B带屏蔽上壳, 顶出PG21, 4耳, 高结构	PG21
T1240165129-000	H16B-TGH-EMC-PG29	H16B EMC HOOD, TOP ENTRY PG29, 4 EAR, HIGH CONSTRUCTION H16B带屏蔽上壳, 顶出PG29, 4耳, 高结构	PG29
T1240165125-000	H16B-TGH-EMC-M25	H16B EMC HOOD, TOP ENTRY M25, 4 EAR, HIGH CONSTRUCTION H16B带屏蔽上壳, 顶出M25, 4耳, 高结构	M25
T1240165132-000	H16B-TGH-EMC-M32	H16B EMC HOOD, TOP ENTRY M32, 4 EAR, HIGH CONSTRUCTION H16B带屏蔽上壳, 顶出M32, 4耳, 高结构	M32
T1240165140-000	H16B-TGH-EMC-M40	H16B EMC HOOD, TOP ENTRY M40, 4 EAR, HIGH CONSTRUCTION H16B带屏蔽上壳, 顶出M40, 4耳, 高结构	M40
PART NUMBER 料 号	DESCRIPTION 描 述		PG/M THREAD PG/M 螺纹孔

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GINO.YAO 04SEP2018		 TE Connectivity	
		CHK CHRIS.WANG 04SEP2018			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME H16B-TGH-EMC-PG/M	
		APVD CHRIS.WANG 04SEP2018 PRODUCT SPEC 108-137016 APPLICATION SPEC 114-137016			
MATERIAL - - -		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		SIZE A2 CAGE CODE 00779 DRAWING NO C-T12401651XX000 RESTRICTED TO -	
		WEIGHT -		SCALE 1:2	
		CUSTOMER DRAWING		SHEET 1 OF 1	
				REV B1	