



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	30NOV2016	DW	CW
	B	ECR-21-106515	21JUL2021	SQ	CW





NOTES:

I. TECHNICAL CHARACTERISTICS:

INSULATION MATERIAL: PC

RATED VOLTAGE: 500V

RATED CURRENT: 16A

INSULATION RESISTANCE: >=400MΩ

RATED IMPULSE VOLTAGE: 6KV

POLLUTION DEGREE: 3


FLAMMABILITY: UL94V-0


MATING CYCLES: 500 CYCLES

WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)

CONTACT FINISH: SILVER PLATED


CONTACT TYPE: DOUBLE SPRING CLAMP






M4 SCREW, RECOMMENDED
TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝, 推荐扭力矩为0.5Nm





PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING,ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸, 仅供参考

T2040485101-000

HE-024-MSS 25-48

HE-024 MALE INSERT,DOUBLE SPRING CLAMP 25-48
HE-024公插,双弹片 25-48

PART NUMBER

料号

PART DESCRIPTION

描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

MATERIAL -

-

DWN DAVID WANG 30NOV2016

CHK CHRIS WANG 30NOV2016

APVD XIANG XU 30NOV2016

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME HE-024-MSS 25-48

SIZE A2

CAGE CODE -

DRAWING NO. ©T2040485101000

RESTRICTED TO

SCALE 1:1

SHEET 1 OF 1

REV B