

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	01FEB2016	DW	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:

INSULATION MATERIAL: PC

FLAMMABILITY: UL94V-0

OPERATION TEMPERATURE: -40°C~+125°C

注释:

1. 技术参数:

绝缘材料: PC

阻燃等级: UL94V-0

工作温度: -40°C~+125°C

T1870102101-000

H10B-RAIL-TOP

H10B INSERT MOUNTING TOP FRAME
H10B 芯件导轨安装支架上部

PART NUMBER

PART DESCRIPTION

料号

描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 01FEB2016

DAVID WANG

CHK 01FEB2016

CHRIS WANG

APVD 01FEB2016

XIANG XU

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME
H10B-RAIL-TOP

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-T1870102101000 -

SCALE 1:1 SHEET 1 OF 1 REV A

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

-

FINISH

-

1470-19 (3/13)