

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION     | DATE      | DWN | APVD |
|---|-----|-----------------|-----------|-----|------|
|   | A   | INITIAL RELEASE | 06SEP2017 | YC  | CW   |
|   |     |                 |           |     |      |
|   |     |                 |           |     |      |

4X M3 SCREW, RECOMMENDED  
TIGHTENING TORQUE 0.5N.m  
4X M3螺丝, 推荐锁紧力矩0.5N.m

M4 SCREW, RECOMMENDED  
TIGHTENING TORQUE 1.2N.m  
M4螺丝, 推荐锁紧力矩1.2N.m

PANEL CUT FOR INSERTS FOR USING  
WITHOUT HOODS/ HOUSINGS  
不使用防护外壳时芯件的安装开孔图

NOTES:

- TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 500V  
RATED CURRENT: 16A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 6KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE: 0.14-4 mm<sup>2</sup> (26-12 AWG)  
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. T20300X20XX-000)

注释:

- 技术参数:  
绝缘材料: PC  
额定电压: 500V  
额定电流: 16A  
绝缘电阻:  $\geq 400M\Omega$   
额定脉冲电压: 6KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围: 0.14-4 mm<sup>2</sup> (26-12 AWG)  
接线类型: 冷压接
- 端子需要单独订购.  
(订货号 T20300X20XX-000)

T2050102201-007

HEE-010-F

HEE-010 FEMALE INSERT  
HEE-010 母插PART NUMBER  
料号PART DESCRIPTION  
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 06SEP2017

YORK CHEN

CHK 06SEP2017

GINO YAO

APVD 06SEP2017

CHRIS WANG

PRODUCT SPEC

108-106137

APPLICATION SPEC

114-106137

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

|        |    |
|--------|----|
| 0 PLC  | ±- |
| 1 PLC  | ±- |
| 2 PLC  | ±- |
| 3 PLC  | ±- |
| 4 PLC  | ±- |
| ANGLES | ±- |

MATERIAL

-

FINISH

-

NAME

HEE-010-F

TE Connectivity

SIZE

A3

CAGE CODE

00779

DRAWING NO

T2050102201007

RESTRICTED TO

-

SCALE  
1:1SHEET  
1 OF 1REV  
A

1470-19 (3/13)