



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14JUL2017	YC	CW
	B	ECR-18-015945	09OCT2018	YC	CW
	B1	ECR-19-019179	30DEC2019	YC	CW
	C	ECR-21-117384	09NOV2021	WQR	CW




THE CODING PINS ARE PACKAGED WITH PRODUCT
编码销与产品一起包装出货



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 830V
RATED CURRENT: 40A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
MATING CYCLES: 500 CYCLES
WIRE RANGE: 1-10 mm² (18-8 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20400X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 830V
额定电流: 40A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6KV
污染等级: 3
插拔次数: 500次
接线范围: 1-10 mm² (18-8 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20400X10XX000)

T2080023101-000	HQ-002-PM	HQ-002 MALE INSERT, HV HQ-002 公插, 高压款
PART NUMBER 产品料号	PART DESCRIPTION 产品描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 14JUL2017 YORK CHEN	 TE Connectivity			
		CHK 14JUL2017 GINO YAO				
DIMENSIONS: mm		APVD 14JUL2017 CHRIS WANG	NAME HQ-002-PM			
		PRODUCT SPEC 108-137310	SIZE A300779			
		APPLICATION SPEC 114-137310				
MATERIAL -		WEIGHT -	DRAWING NO T2080023101000			
		CUSTOMER DRAWING	SCALE 3:2		SHEET 1 OF 1	REV C