

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20




© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10JUL2018	RG	CW
	A1	ECR-19-004303	20MAR2019	CH	CW
	B	ECR-20-014388	04DEC2020	WQR	CW
	B1	ECR-21-105138	30JUN2021	WQR	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED, DEEP GREY
OPERATION TEMPERATURE: -40-+125°C
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
表面处理: 粉末涂层, 深灰色
工作温度: -40-+125°C
防护等级: IP65(配合)



T1A90160229-000	H16B-TGH/TFH-2PG29	H16B HOOD, TOP ENTRY PG29, FRONT ENTRY PG29, 4 EAR HIGH CONSTRUCTION, POWDER COATED, DEEP GREY H16B上壳, 顶出PG29, 前出PG29, 4耳, 高结构, 深灰色粉末喷涂	2XPG29
PART NUMBER 料号	DESCRIPTION 描述		PG/M THREAD PG/M 螺纹孔
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 9JUL2018 Robert Gan	TE Connectivity
		CHK 9JUL2018 Gino Yao	
		APVD 9JUL2018 Chris Wang	
		PRODUCT SPEC 108-137013	
		APPLICATION SPEC 114-137013	NAME H16B-TGH/TFH-M/PG
		WEIGHT -	
		CUSTOMER DRAWING	SCALE 1:2
			SHEET 1 OF 1
			REV B1