


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	INITIAL	11AUG2016	CW
	A1	ECR-17-001649	07FEB2017	CW
	B	ECR-21-106515	21JUL2021	CW



1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC(GREY)
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP



PANEL CUT OUT FOR INSERTS FOR
USE WITHOUT HOODS/HOUSING
不使用防护外壳时元件的安装开孔图

T2040165201-000	HE-016-FSS	HE-016 FEMALE INSERT, DOUBLE SPRING CLAMP HE-016母插, 双弹片压接
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11AUG2016 CHARLIE HU CHK 11AUG2016 KYLE ZENG APVD 11AUG2016 CHRIS WANG		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HE-016-FSS	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-137044 APPLICATION SPEC 114-137044	
MATERIAL -		WEIGHT -		SIZE A2	CAGE CODE -
		CUSTOMER DRAWING		DRAWING NO C-T2040165201000	RESTRICTED TO -
				SCALE 3:2	SHEET 1 OF 1
				REV B	