

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20







COPYRIGHT 20

BY -



ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	13JUL2016	YC	CW
	B	ECR-21-109485	12AUG2021	BS	CW



10X M3 SCREW
RECOMMENDED TIGHTENING TORQUE 0.5Nm
10X M3螺丝, 推荐拧紧力矩0.5Nm



PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PA
RATED VOLTAGE: 500 V
RATED CURRENT: 30 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-4 mm² (20-12 AWG)
CONTACT TYPE: SCREW CRIMP (M3)

注释:

1. 技术参数:
绝缘材料: PA
额定电压: 500 V
额定电流: 30 A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 6 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.5-4 mm² (20-12 AWG)
接线类型: 螺钉压接 (M3)

T2100102101-000

HCC-010-M
HCC-010 公插, 单排

PART NUMBER
料号

PART DESCRIPTION
描述



TE Connectivity

NAME
HCC-010-M

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-T2100102101000

DWN 13JUL2016

YORK CHEN

CHK 13JUL2016

KYLE ZENG

APVD 13JUL2016

CHRIS WANG

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

SCALE 1:1


SHEET 1 OF 1

REV B

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC

±-

1 PLC

±-

2 PLC

±-

3 PLC

±-

4 PLC

±-

ANGLES

±-

FINISH

-

-