



NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 500V
RATED CURRENT: 16A
INSULATION RESISTANCE: $\geq 400\text{M}\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.5\text{mm}^2 \sim 2.5\text{mm}^2$ (AWG20-AWG14)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: DOUBLE SPRING CLAMP

注释：

技术参数：
绝缘材料：PC
额定电压：1500V
额定电流：16A
绝缘电阻： $\geq 400M\Omega$
脉冲电压：6KV
污染等级：3
阻燃等级：UL94V-0
插拔次数：500次
接线范围： $0.5mm^2 \sim 2.5mm^2$ （AWG20-AWG14）
端子表面处理：镀银
接线类型：双弹片连接



T2040325201-000		HE-016-FSS 17-32		HE-016 FEMALE INSERT,DOUBLE SPRING CLAMP 17-32 HE-016母插,双弹片 17-32			
PART NUMBER 料号		PART DESCRIPTION 描述					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28NOV2016 DAVID WANG CHK 28NOV2016 CHRIS WANG APVD 28NOV2016 XIANG XU PRODUCT SPEC 108-137044 APPLICATION SPEC 114-137044		 TE Connectivity			
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		NAME HE-016-FSS 17-32			
MATERIAL -		WEIGHT -		SIZE A2	CAGE CODE -	DRAWING NO C-T2040325201000	RESTRICTED TO -
CUSTOMER DRAWING					SCALE 3:2	SHEET 1 OF 1	REV B