

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	18SEP2017	YC	CW
	C	ECR-22-158463	05JAN2023	BS	CW
	D	ECR-23-168984	21MAR2023	BS	CW

NOTES:

- TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 1000V  
RATED CURRENT: 70A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 8KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE: 10~25 mm<sup>2</sup>  
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T2400001XX0000)

注释:

- 技术参数:  
绝缘材料: PC  
额定电压: 1000V  
额定电流: 70A  
绝缘电阻:  $\geq 400M\Omega$   
额定脉冲电压: 8KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围: 10~25 mm<sup>2</sup>  
接线类型: 冷压接
- 端子需要单独订购.  
(订货号参考图面: T2400001XX0000)

T2111020101-007	HMN-002-MC	HMN-002 MALE MODULE INSERT, CRIMP HMN-002 冷压模块公插
-----------------	------------	---

PART NUMBER 料号
-------------------

PART DESCRIPTION 描述
------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 18SEP2017

YORK CHEN

CHK 18SEP2017

GINO YAO

APVD 18SEP2017

CHRIS WANG

PRODUCT SPEC

108-137059

APPLICATION SPEC

114-137059

WEIGHT

-

CUSTOMER DRAWING

NAME  
HMN-002-MC

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-T2111020101007 -

SCALE SHEET 1 OF 1 REV D

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL FINISH

-

1470-19 (3/13)