

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITAIL	19SEP2017	YC	CW

NOTES:

- TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 500V  
RATED CURRENT: 16A  
INSULATION RESISTANCE:  $\geq 400M\Omega$   
RATED IMPULSE VOLTAGE: 6KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
MATING CYCLES: 500 CYCLES  
WIRE RANGE: 0.14~4.0 mm<sup>2</sup> (26~12 AWG)  
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T20300X20XX000)

注释:

- 技术参数:  
绝缘材料: PC  
额定电压: 500V  
额定电流: 16A  
绝缘电阻:  $\geq 400M\Omega$   
额定脉冲电压: 6KV  
污染等级: 3  
阻燃等级: UL94V-0  
插拔次数: 500次  
接线范围: 0.14~4.0 mm<sup>2</sup> (26~12 AWG)  
接线类型: 冷压接
- 端子需要单独订购.  
(订货号参考图面: T20300X20XX000)

T2111202201-007	HMN-020-F	HMN-020 FEMALE MODULE INSERT HMN-020 模块母插	
PART NUMBER 料号		PART DESCRIPTION 描述	
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DIMENSIONS: mm 			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		NAME HMN-020-F	
MATERIAL		PRODUCT SPEC 108-137063 APPLICATION SPEC 114-137063	
FINISH		WEIGHT -	
-		SIZE A3	
-		CAGE CODE 00779	
-		DRAWING NO T2111202201007	
-		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 1:1	
		SHEET 1 OF 1	
		REV B	

1470-19 (3/13)