


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	28APR2018	DW	CW
	B	ECR-18-012226	01SEP2018	DW	CW
	C	ECR-23-195672	23MAY2024	BS	CW



NOTES:

I. TECHNICAL CHARACTERISTICS:

HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY,
POWDER COATED,GRAY

RATED VOLTAGE: 500 V

RATED CURRENT: 16 A

RATED IMPULSE VOLTAGE: 6 KV

POLLUTION DEGREE: 3

FLAMMABILITY: UL94V-0

MATING CYCLES: 500 CYCLES

WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)

CONTACT TYPE: SPRING CRIMP CONTACT

1. 技术参数:

- 壳体材料: 铝合金, 灰色粉末喷涂
- 额定电压: 500V
- 额定电流: 16A
- 额定脉冲电压: 6 KV
- 污染等级: 3
- 阻燃等级: UL94V-0
- 插拔次数: 500次
- 接线范围: 0.5-2.5 mm² (20-14 AWG)
- 接线类型: 弹片型

