

NOTES:

TECHNICAL CHARACTERISTICS:

HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY,
POWDER COATED, GRAY

DEGREE OF PROTECTION:

IP65 (MATED WITH HOOD)

IP54 (MATED WITH PROTECTION COVER)

RATED VOLTAGE: 500V

RATED CURRENT: 16A

RATED IMPULSE VOLTAGE: 6KV

POLLUTION DEGREE: 3



FLAMMABILITY: UL94V-0


MATING CYCLES: 500 CYCLES

WIRE RANGE: 0.5-2.5 mm2 (20-14 AWG)

CONTACT TYPE: SPRING CRIMP CONTACT

This diagram shows the exploded view of the ECU housing assembly. The top part is the lid, which has four screws and four pins. The bottom part is the main housing, which has a central slot for the lid and two side flaps. The lid is shown being placed onto the main housing.



T2120100223-000		ZGG-10DST (1-6/3-4/5-10)		HIOB ELEVATOR MAINTENANCE BOX INCLUDING INSERT (1-6/3-4/5-10) HIOB 电梯检修插座含芯件 (1-6/3-4/5-10)			
PART NUMBER 零件料号		PART DESCRIPTION 零件描述					
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm  MATERIAL - -	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		DWN 21MAY2018 DAVID WANG CHK 21MAY2018 GINO YAO APVD 21MAY2018 CHRIS WANG	 TE Connectivity			
			PRODUCT SPEC	NAME ZGG-10DST (1-6/3-4/5-10)			
			APPLICATION SPEC				
			WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO. C-T2120100223000	RESTRICTED TO -
	FINISH -		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV C