






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	13AUG2018	GY	CW



- NOTES:
1. TECHNICAL CHARACTERISTICS:
RATED VOLTAGE: 50V
RATED CURRENT: 5A
INSULATION RESISTANCE: $\geq 100M\Omega$
RATED IMPULSE VOLTAGE: 0.8KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
WIRE RANGE: 0.08~0.52 mm² (28~20 AWG)
CONTACT TYPE: CRIMP CONTACT
 2. CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20700X10XX000)

- 注释:
1. 技术参数:
额定电压: 50V
额定电流: 5A
绝缘电阻: $\geq 100M\Omega$
额定脉冲电压: 0.8KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40\sim+125^{\circ}C$
接线范围: 0.08~0.52 mm² (28~20 AWG)
接线类型: 冷压接
 2. 端子需要单独订购.
(订货号参考图面: T20700X10XX000)

T2111092003-000		D-Sub-09,M		D-Sub 9PIN MALE MODULE D-Sub 9针公连接器	
PART NUMBER 料 号		PART DESCRIPTION 描 述			
OWN 13AUG2018 GINO.YAO		TE Connectivity			
CHK 13AUG2018 CHRIS.WANG					
APVD 13AUG2018 CHRIS.WANG					
PRODUCT SPEC 108-137064		NAME D-Sub-09,M			
APPLICATION SPEC 114-137064					
WEIGHT -		SIZE A3	CAGE CODE 00779	DRAWING NO C-T2111092003000	RESTRICTED TO
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV A

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
MATERIAL -	FINISH -