

printed on 8 May 2024 17:17 (China Standard Time) from TE343936



© 2023 TE Connectivity. All Rights Reserved.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16OCT2023	AD	CW
	A1	ECR-24-208147	08MAY2024	AD	CW

NOTES:
1. TECHNICAL CHARACTERISTICS:
CONTACT MATERIAL: BRASS ALLOY
SURFACE TREATMENT: GOLD PLATING
CONTACT RESISTANCE: $\leq 15m\Omega$
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0235-000-000
LOCATOR FOR DIGITAL CRIMPING TOOL:
TE PART NO.: C0-0265-000-000

注释:
1. 技术参数:
针件材料: 铜合金
表面处理: 镀金
接触电阻: $\leq 15m\Omega$
工作温度: $-40\sim+125^{\circ}C$
数码压接工具:
TE料号: C0-0235-000-000
数码压接工具的定位器:
TE料号: C0-0265-000-000



T2400011002-000	ETH-CP-0.6	ETHERNET PIN CONTACT $\varnothing 0.6MM$, GOLD PLATED, CRIMP 以太网公端子 $\varnothing 0.6$, 镀金, 压接
PART NUMBER 料 号	PART DESCRIPTION 描 述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Alan Dong 16OCT2023	 TE Connectivity								
DIMENSIONS: mm		CHK Gino Yao 16OCT2023	NAME ETHERNET PIN CONTACT CALIBER 0.6MM								
		APVD Chris Wang 16OCT2023									
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-137683							
MATERIAL - -		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APPLICATION SPEC 114-137683		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		FINISH - -		WEIGHT 0.09 g		A3	00779	Ⓒ-T2400011002000	-		
CUSTOMER DRAWING						SCALE	10:1	SHEET	1 OF 1	REV	A1