






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	26 JUL 2016	GY	CW
	B	ECR-17-004266	04 APR 2017	GY	CW
	B1	ECR-17-008106	10 JUN 2017	RL	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
SHELL MATERIAL: PA
SEAL MATERIAL: ELASTIC RUBBER
PINCH RING MATERIAL: ELASTIC RUBBER
PROTECTION DEGREE: IP65
WIRE RANGE: SEE TABLE

技术指标:
1. 技术参数:
主体材料: 尼龙
密封件材料: 弹性橡胶
夹紧件材料: 弹性橡胶
防护等级: IP65
夹线范围: 见表格



	M32X1.5	4*Ø9	46.6	39	11	42	DLX-32-2KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M32 (4*9) 多孔塑料接头 M32 (4*9)	T3229320202-000
	M25X1.5	4*Ø6	36.5	31.5	11	33	DLX-25-1KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M25 (4*6) 多孔塑料接头 M25 (4*6)	T3229250102-000
	M25X1.5	2*Ø8	36.5	31.5	11	33	DLX-25-4KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M25 (2*8) 多孔塑料接头 M25 (2*8)	T3229250402-000
	M25X1.5	2*Ø6	36.5	31.5	11	33	DLX-25-3KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M25 (2*6) 多孔塑料接头 M25 (2*6)	T3229210301-000
	M20X1.5	2*Ø5	27	26.5	9	24	DLX-20-KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M20 (2*5) 多孔塑料接头 M20 (2*5)	T3229200202-000
	M16X1.5	2*Ø3	21	22	8	19	DLX-16-KPM	MULTIPLE SEALING INSERT NYLON CABLE GLAND M16 (2*3) 多孔塑料接头 M16 (2*3)	T3229160102-000
	PG36	5*Ø9	59	48.5	13	53	DLX-36-1KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG36 (5*9) 多孔塑料接头 PG36 (5*9)	T3229360101-000
Obsolete	PG29	3*Ø9	47	37.2	10.5	42	DLX-29-3KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG29 (3*9) 多孔塑料接头 PG29 (3*9)	T3229290301-000
	PG29	4*Ø9	47	39	11	42	DLX-29-2KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG29 (4*9) 多孔塑料接头 PG29 (4*9)	T3229290201-000
	PG21	2*Ø8	37	31.5	11	33	DLX-21-4KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG21 (2*8) 多孔塑料接头 PG21 (2*8)	T3229210401-000
Obsolete	PG21	2*Ø6	36.8	32.3	9.7	33	DLX-21-3KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG21 (2*6) 多孔塑料接头 PG21 (2*6)	T3229210301-000
	PG16	2*Ø6	30	28	10	27	DLX-16-KPMS	MULTIPLE SEALING INSERT NYLON CABLE GLAND PG16 (2*6) 多孔塑料接头 PG16 (2*6)	T3229160201-000
	AG	WIRE RANG 夹线范围(Ø)	ØW	H	GL	SW	DESCRIPTION 产品描述		PART NUMBER 成品料号

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GINO.YAO 26JUL2016	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK CHRIS.WANG 26JUL2016		
DIMENSIONS:		APVD XIANG.YU 26JUL2016	NAME MULTIPLE SEALING INSERT NYLON CABLE GLAND	
mm		PRODUCT SPEC		
		APPLICATION SPEC		
		ANGLES		
MATERIAL	FINISH	WEIGHT	SIZE A1	CAGE CODE -
-	-	-	DRAWING NO T3229XXXXX000	RESTRICTED TO -
-	-	CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
			REV B1	