






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL VERSION RELEASE	28SEP2023	F.Y	C.W




- NOTE:
- MATERIAL:
CONTACT BODY: COPPER ALLOY
LOCKING SPRING: STAINLESS STEEL
 - SURFACE PLATING:
a) NICKEL UNDERPLATING, GOLD PLATING AT CONTACT AREA, TIN PLATING AT OTHER AREA.
b) NICKEL UNDERPLATING, TIN PLATING OVERALL.
 - PACKAGE: 4000PCS/REEL, 8000PCS/BOX

- 注释
- 材料
端子主体：铜合金
锁扣弹片：不锈钢
 - 电镀规格：
a) 底镀镍，接触区镀金，其他区域镀锡
b) 底镀镍，全镀锡
 - 包装：4000pcs/卷，8000pcs/箱



SECTION D-D
SCALE 10:1



SECTION E-E
SCALE 10:1

Ø 2.7	4.27	4.20	Ø 1.10	2.41	2.28	(b)	Ø 1.0MM MALE STAMPING CONTACT TIN PLATED, 0.50~0.75MM ² ,	T2210001010-011
						(a)	Ø 1.0MM MALE STAMPING CONTACT GOLD PLATED, 0.50~0.75MM ²	T2210001010-010
Ø 2.6	4.27	4.20	Ø 0.80	1.75	1.85	(b)	Ø 1.0MM MALE STAMPING CONTACT TIN PLATED, 0.20~0.35MM ²	T2210001010-001
						(a)	Ø 1.0MM MALE STAMPING CONTACT GOLD PLATED, 0.20~0.35MM ²	T2210001010-000
DIM.F	DIM.E	DIM.D	DIM.C	DIM.B	DIM.A	SURFACE PLATING	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN FENCER YU 28SEP2023	 TE Connectivity					
				CHK CHRIS WANG 28SEP2023						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD CHRIS WANG 28SEP2023	NAME	DIA1.0MM MALE STAMPING CONTACT				
		0 PLC ±0.50		PRODUCT SPEC	-					
		1 PLC ±0.30		108-137685						
		2 PLC ±0.20		APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
		3 PLC ±		114-137685	A2	00779	C=T22100010100XX		-	
		4 PLC ±								
MATERIAL SEE NOTE		FINISH		WEIGHT						
		-		-						
		-		CUSTOMER DRAWING	SCALE		SHEET		REV	
						6:1		1 OF 1		A