


TECHNICAL DATA

	T411001X02X-000	T411001X03X-000	T411001X04X-000	T411001X05X-00X	T411001208X-00X
RATED VOLTAGE	250V	250V	250V	60V	30V
RATED CURRENT	4A	4A	4A	4A	2A
POLLUTION DEGREE	3	3	3	3	3
OVERVOLTAGE CATEGORY	II	II	II	II	II
CONTACT RESISTANCE	≤10mΩ	≤10mΩ	≤10mΩ	≤10mΩ	≤10mΩ
INSULATION RESISTANCE	>100MΩ	>100MΩ	>100MΩ	>100MΩ	>100MΩ
DEGREE OF PROTECTION	IP67	IP67	IP67	IP67	IP67
OPERATION TEMPERATURE	-40~85℃	-40~85℃	-40~85℃	-40~85℃	-40~85℃



PIN ARRANGEMENT A-CODE

T411001X02X-000	T411001X03X-000	T411001X04X-000
T411001X05X-00X	T411001208X-00X	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Nick Pan 24AUG2015	TE Connectivity			
DIMENSIONS:		CHK Kobby Zhao 24AUG2015	NAME M12 FEMALE, A CODE, STRAIGHT SHIELDED CONNECTOR SCREW TERMINAL			
mm		APVD Xiang Xu 24AUG2015				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-106140	SIZE A2			
0 PLC ±-		APPLICATION SPEC 114-137144				
1 PLC ±0.25		WEIGHT -	CAGE CODE -			
2 PLC ±0.15		CUSTOMER DRAWING				
3 PLC ±-		SCALE 1:1	DRAWING NO. C-T411001XXXX000			
4 PLC ±-		SHEET 1 OF 1				
ANGLES ±-		REV B1				
FINISH -						