



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	27JUN2016	GY	CW






WITH TE LOGO
成品料号 (带TE Logo)



WITHOUT TE LOGO
成品料号 (不带TE Logo)

NOTES / 技术指标:

- I. TECHNICAL CHARACTERISTICS / 技术参数:
- SHELL MATERIAL / 主体材料 : NICKEL PLATED BRASS / 铜镀镍
 - SEAL MATERIAL / 密封材料: NBR
 - PINCH RING MATERIAL / 夹紧件材料: PA
 - OPERATION TEMPERATURE / 工作温度: - 40°C - +100°C
 - PROTECTION DEGREE / 防护等级: IP68
 - WIRE RANGE / 夹线范围: SEE TABLE / 见表格



13-20	DLX-MS-PG21-PG29	METAL CABLE GLAND (PG21-PG29)(13-20) 金属电缆接头(PG21-PG29)(13-20)	T3619212901-000	T3619212901-001
WIRE RANG 夹线范围 (Ø)	DESCRIPTION 产品描述		PART NUMBER WITH TE LOGO 成品料号 (带TE Logo)	PART NUMBER WITHOUT TE LOGO 成品料号 (不带TE Logo)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GINO.YAO 24JUN2016	TE Connectivity DLX-MS-PG21-PG29 METAL CABLE GLAND		
DIMENSIONS: mm		CHK CHRIS.WANG 24JUN2016			
		APVD XIANG.XU 24JUN2016			
		PRODUCT SPEC			
MATERIAL	FINISH	APPLICATION SPEC	NAME		
		-	SIZE		
		WEIGHT	CAGE CODE		
-	-	-	DRAWING NO		
-	-	CUSTOMER DRAWING	RESTRICTED TO		
		SCALE	SHEET		REV
		1:1	1 OF 1		A