



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	04MAR2024	AN	VN

PART AS SUPPLIED



PRODUCT DIMENSIONS

SIZES	D		W	
	mm.	in.	mm.	in.
TSAS-NR500	1.40±0.20	0.055±0.008	0.50±0.10	0.020±0.004
TSAS-NR501	2.30±0.25	0.091±0.010	0.60±0.15	0.024±0.006
TSAS-NR502	2.90±0.25	0.114±0.010	0.75±0.20	0.030±0.008
TSAS-NR503	4.00±0.40	0.157±0.016	0.75±0.20	0.030±0.008


PRODUCT INFORMATION

- MATERIAL: FLEXIBLE HOT-MELT ADHESIVE
- COLOUR: AMBER
- BROOKFIELD VISCOSITY AT 160°C; 55 TO 85 Pas
TEMPERATURE RATING 125°C
- SPECIFIC CUT LENGTHS CAN BE SUPPLIED FROM THE
PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.1
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN	04MAR2024
CHK	AYESHABANU N
APVD	04MAR2024
NAME	BASAVARAJA D A
PRODUCT SPEC	VLADIMIR NEMEC
APPLICATION SPEC	-
WEIGHT	114-120023
CUSTOMER DRAWING	-



NAME
TSAS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	TSAS	-
SCALE	SHEET	OF	REV
NTS	1	1	A